



Precision ESD Safe Conductive Drivers

Wiha Precision ESD Static Dissipative Screwdrivers meet the requirements for tools used in electrostatic sensitive areas.



Rotating cap for precise turning & control with fingertip

Molded Precision handle of impact resistant conductive material

Tapered handle allows rapid rotation

Blade, CVM steel, hardened, hard chrome finish

Tip, precision ground for exact fit, Wiha Chromtop finish

Surface resistance of handles is $10^6 - 10^9$ Ohms



272 Slotted Screwdriver, With Precision ESD Safe Conductive Handle. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, conductive material.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	Each
272 08	.08	1/32	40	1.6	0.16	.007	120	4.72	.02	10	\$5.52
272 10	1.0	.039	40	1.6	0.18	.007	120	4.72	.02	10	\$5.52
272 12	1.2	3/64	40	1.6	0.20	.008	120	4.72	.02	10	\$5.52
272 15	1.5	1/16	40	1.6	0.25	.010	120	4.72	.02	10	\$5.52
272 20	2.0	5/64	40	1.6	0.40	.016	120	4.72	.02	10	\$4.66
272 22	2.0	5/64	75	3.0	0.40	.016	155	6.08	.03	10	\$5.18
272 23	2.0	5/64	100	4.0	0.40	.016	180	7.09	.03	10	\$5.70
272 24	2.0	5/64	150	6.0	0.40	.016	260	10.24	.04	10	\$6.22
272 25	2.5	3/32	50	2.0	0.40	.016	145	5.71	.04	10	\$4.82
272 27	2.5	3/32	100	3.9	0.40	.016	195	7.68	.03	10	\$5.70
272 28	2.5	3/32	150	6.0	0.40	.016	245	9.61	.04	10	\$6.22
272 30	3.0	1/8	50	2.0	0.50	.020	145	5.71	.04	10	\$4.82
272 32	3.0	1/8	100	4.0	0.50	.020	210	8.27	.04	10	\$5.18
272 34	3.0	1/8	150	6.0	0.50	.020	260	10.24	.05	10	\$6.22
272 35	3.5	9/64	60	2.4	0.60	.024	170	6.69	.06	10	\$5.20
272 37	3.5	9/64	100	3.9	0.60	.024	210	8.27	.06	10	\$5.70
272 38	3.5	9/64	150	6.0	0.60	.024	260	10.24	.06	10	\$6.22
272 40	4.0	5/32	60	2.4	0.80	.031	170	6.69	.06	10	\$5.56
272 42	4.0	5/32	100	3.9	0.80	.031	210	8.27	.06	10	\$5.80
272 43	4.0	5/32	150	6.0	0.80	.031	260	10.24	.07	10	\$6.32



272 90 Set 8 Pcs. Slotted Precision ESD Safe Conductive Handle. Blade CVM steel, hardened, hard chromed. Handle impact resistant, conductive material. In storage pouch

Item No.	mm	mm	mm	mm	lbs.
272 90	272 08	.08	40	272 20	2.0 40
	272 10	1.0	40	272 25	2.5 50
	272 12	1.2	40	272 30	3.0 50
	272 15	1.5	40	272 35	3.5 60
					Each \$45.64



273 90 Set 7 Pcs. Slotted & Phillips Precision ESD Safe Conductive Handle. Blade high alloy CVM steel, hardened, hard chromed. Handle manufactured from impact resistant, conductive material.

Item No.	mm	mm	Size	mm	lbs.
273 90	272 15	1.5	40	273 05	00 40
	272 20	2.0	40	273 10	0 50
	272 25	2.5	50	273 20	1 60
	272 35	3.5	60		Each \$34.30

Precision ESD Safe Slotted/Phillips Drivers



273 Phillips Screwdriver, With Precision ESD Safe Conductive Handle. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, conductive material.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	Each
273 02	000	40	1.6	2.0	.079	120	4.7	.02	10	\$7.50
273 05	00	40	1.6	2.0	.079	120	4.7	.02	10	\$5.30
273 07	00	75	3.0	2.0	.079	155	6.1	.02	10	\$6.34
273 10	0	50	2.0	3.0	.118	145	5.7	.04	10	\$5.00
273 12	0	75	3.0	3.0	.118	170	6.7	.03	10	\$5.90
273 14	0	100	4.0	3.0	.118	195	7.6	.05	10	\$6.22
273 16	0	150	5.9	3.0	.118	245	9.6	.06	10	\$6.54
273 20	1	60	2.3	4.0	.157	170	6.7	.06	10	\$5.08
273 22	1	75	3.0	4.0	.157	155	6.1	.06	10	\$5.86
273 24	1	100	3.9	4.0	.157	210	8.2	.06	10	\$6.22
273 26	1	150	5.9	4.0	.157	260	10.2	.07	10	\$6.54



273 99 Set 8 Pcs. Slotted & Phillips Precision ESD Safe Conductive Handle. Blade high alloy CVM steel, hardened, hard chromed. Handle manufactured from impact resistant, conductive material. In storage pouch

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
273 99	272 15	1.5	40	273 02	000	40	10	\$47.20
	272 20	2.0	40	273 05	00	40	10	
	272 25	2.5	50	273 10	0	50	10	
	272 30	3.0	50	273 20	1	60	10	



273 93 Set 7 Pcs. Extra Long Slotted & Phillips Precision ESD Safe Conductive Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, conductive material.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
273 93	272 24	2.0	150	273 16	0	150	10	\$44.70
	272 28	2.5	150	273 26	1	150	10	
	272 34	3.0	150				10	
	272 38	3.5	150				10	
	272 43	4.0	150				10	



911 18 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.	Each
911 18	14 1/2" W x 7 3/4" L	.13	1	\$6.22