

Search Results

Evaluate  
 - FAQ's  
 - Product Bulletins  
 - PDF-Opti-Core Fi ..

How to Buy  
 - Bill of Material  
 - Favorite Products List  
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'FZOB3-NM1'

Your search criteria matched only one product, shown below

**FZOB3-NM1**



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Backward compatible for use with all 50/125µm system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

<sup>1</sup>Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FZPE10-10M1) with the desired length (FZPE10-10M2 for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

• Part Number	FZOB3-NM1
• RoHS Compliance Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	SC to Pigtail Patch Cord, Optimized OM4, 0.15 dB IL Loss, Simplex Pigtails, 900µ Buffered Fiber – 1m.
• Product Type	SC Patch Cords
• Length (m)	1
• Fiber Compatibility	10 GbE 50/125µ
• Fiber Cable Size	900µ
• Fiber Cable Type	Buffered Fiber
• Fiber Type	Multimode
• Connector 1 Type	SC Connector
• Connector 2 Type	Pigtail
• End Configurations	SC to Pigtail
• Fiber Count	1
• Flammability Rating	Riser (OFNR)
• Pricing Description	SC to Pigtail, Optimized OM4, Simplex Pigtails, 900µ Buffered Fiber, 1M
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.