

Ferrules




Fig. 1 — Insulated




Fig. 2 — Uninsulated




Fig. 3 — Dual Wire Insulated

Insure reliable electrical connections and prevent fraying and breaking of wire strands when terminating conductors in screw clamp terminal blocks. Insulated ferrules have molded-on plastic sleeves and prevent conductor breakage due to bending, wire stress or vibration.

Ferrules, Insulated — Fig. 1. Sleeve: Tin-plated copper. Tube: Polypropylene.

Stock No.	Mfr.'s Type	Color	Wire Size AWG	Strip Length A	Ferrule Length B	Use with Crimping Tool	PER PK./100
502-5200	2620.0	Lt. Blue	24	0.24"	0.39"	PZU6	8.57
502-5202	2621.0	Lt. Blue	24	0.31"	0.47"	PZU6	8.57
502-5204	2622.0	Turq.	22	0.24"	0.39"	PZU6	8.57
502-5206	2623.0	Turq.	22	0.31"	0.47"	PZU6	8.57
502-5208	2397.0	Orange	20	0.24"	0.47"	PZU6	8.57
502-2110	2201.0	Orange	20	0.31"	0.55"	PZU6	8.57
502-5210	2398.0	White	20	0.24"	0.47"	PZU6	8.57
502-2112	2202.0	White	20	0.31"	0.55"	PZU6	8.57
502-5212	2399.0	Yellow	18	0.24"	0.47"	PZU6	9.69
502-2114	2203.0	Yellow	18	0.31"	0.55"	PZU6	10.61
502-2116	2204.0	Red	16	0.31"	0.55"	PZU6	10.61
502-5214	2400.0	Red	16	0.39"	0.63"	PZU6	11.72
502-5216	2205.0	Red	16	0.71"	0.94"	PZU6	11.72
502-2118	2206.0	Blue	14	0.31"	0.55"	PZU6	12.12
502-5218	2401.0	Blue	14	0.47"	0.71"	PZU6	21.00
502-5220	2207.0	Blue	14	0.71"	0.94"	PZU6	23.01
502-2120	2208.0	Gray	12	0.39"	0.67"	PZU6	18.18
502-5223	2402.0	Gray	12	0.47"	0.79"	PZU6	23.14
502-5226	2209.0	Gray	12	0.71"	1.02"	PZU6	26.00
502-5228	2210.0	Black	10	0.47"	0.79"	PZU6	24.00
502-5230	2211.0	Black	10	0.71"	1.02"	PZU6	28.00
502-5232	2212.0	Ivory	8	0.47"	0.87"	PZU16	26.00
502-5234	2213.0	Ivory	8	0.71"	1.10"	PZU16	32.93
502-5236	2214.0	Green	6	0.47"	0.94"	PZU16	30.00
502-5238	2215.0	Green	6	0.71"	1.10"	PZU16	41.00
502-5240	2267.0	Brown	4	0.71"	1.18"	PZU35	71.00
502-5242	2272.0	Brown	4	0.87"	1.42"	PZU35	76.00
502-5244	2276.0	Beige	2	0.71"	1.18"	PZU35	102.00
502-5246	2390.0	Beige	2	0.98"	1.54"	PZU35	116.89
502-5248	2500.0	Olive	1	0.79"	1.42"	PZU50	134.00
502-5250	2786.0	Yellow	2/0	0.79"	1.46"	†	150.00
502-5252	2787.0	Red	3/0	0.98"	1.73"	†	165.00
502-5254	2788.0	Blue	4/0	1.06"	1.89"	†	181.90
502-5256	2789.0	Yellow	250MCM	1.26"	2.28"	†	191.00

†Consult Allied.

Ferrule Box Assortment

Circular plastic box, supplied with five different size ferrules. Clear rotary cover allows for easy dispensing. **Box Contains:** 50 each, H0.5/14 Orange; 100 each, H0.75/14 White; 100 each, H1.0/12 Yellow; 100 each, H1.5/14 Red; 50 each, H2.5/14 Blue.



502-5316. 2884.9.....EACH 43.00

Dual wire insulated ferrules provide reliable connection of multiple wires into the same terminal block clamp and simplify jumping between terminal blocks. All ferrules are packaged in 100/piece standard packs.

Ferrules, Uninsulated — Fig. 2. Tin-plated copper.

Stock No.	Mfr.'s Type	Color	Wire Size AWG	Strip Length A	Ferrule Length B	Use with Crimping Tool	PER PK./100
502-2150	2216.0	—	20	0.24"	0.24"	PZU6	4.37
502-5258	2217.0	—	20	0.24"	0.24"	PZU6	4.37
502-2152	2218.0	—	20	0.39"	0.39"	PZU6	5.51
502-5260	2219.0	—	18	0.24"	0.24"	PZU6	5.51
502-2154	2220.0	—	18	0.39"	0.39"	PZU6	5.51
502-2156	2221.0	—	16	0.28"	0.28"	PZU6	5.51
502-5262	2222.0	—	16	0.39"	0.39"	PZU6	5.84
502-2158	2223.0	—	14	0.28"	0.28"	PZU6	6.43
502-5264	2224.0	—	14	0.47"	0.47"	PZU6	7.55
502-2160	2225.0	—	12	0.35"	0.35"	PZU6	6.27
502-2161	2226.0	—	12	0.47"	0.47"	PZU6	7.45
502-5266	2227.0	—	10	0.47"	0.47"	PZU6	10.61
502-5268	2388.0	—	10	0.59"	0.59"	PZU6	11.56
502-5270	2228.0	—	8	0.47"	0.47"	PZU16	12.73
502-5272	2389.0	—	8	0.59"	0.59"	PZU16	12.60
502-5274	2229.0	—	8	0.71"	0.71"	PZU16	13.84
502-5276	2391.0	—	6	0.47"	0.47"	PZU16	15.96
502-5278	2392.0	—	6	0.59"	0.59"	PZU16	18.08
502-5280	2393.0	—	6	0.71"	0.71"	PZU16	21.00
502-5282	2394.0	—	4	0.59"	0.59"	PZU35	32.60
502-5284	2395.0	—	4	0.71"	0.71"	PZU35	39.82
502-5286	2396.0	—	2	0.71"	0.71"	PZU35	47.00
502-5288	2816.0	—	1	1.26"	1.26"	PZU50	71.30
502-5290	2790.0	—	2/0	1.02"	1.02"	†	88.00
502-5292	2791.0	—	3/0	1.18"	1.20"	†	115.00
502-5294	2792.0	—	4/0	1.26"	1.26"	†	140.00
502-5296	2793.0	—	250MCM	1.50"	1.57"	†	170.00
502-5298	2815.0	—	350MCM	1.57"	1.57"	†	53.57*

Dual Wire Ferrules, Insulated — Fig. 3. Sleeve: Tin-plated copper. Tube: Polypropylene. Each dual wire ferrule accepts 2 wires of equal size.


502-4262	2794.0	White	2/22	0.43"	0.57"	PZU6	10.20
502-4264	2775.0	Gray	2/20	0.43"	0.57"	PZU6	11.11
502-5300	2795.0	Gray	2/20	0.51"	0.65"	PZU6	11.51
502-5303	2776.0	Red	2/18	0.51"	0.79"	PZU6	13.83
502-4268	2777.0	Black	2/16	0.47"	0.62"	PZU6	15.15
502-5304	2797.0	Black	2/16	0.63"	0.77"	PZU6	16.16
502-4270	2778.0	Blue	2/14	0.55"	0.73"	PZU6	23.01
502-5319	2798.0	Blue	2/14	0.67"	0.81"	PZU6	25.03
502-5309	2799.0	Gray	2/12	0.63"	0.87"	PZU16	27.00
502-5311	2800.0	Yellow	2/10	0.75"	0.91"	PZU16	30.00
502-5313	2801.0	Red	2/8	0.75"	0.94"	PZU16	36.00
502-5315	2802.0	Blue	2/6	0.55"	1.14"	PZU16	37.00
502-5302	2796.0	Red	2/18	0.51"	0.99"	PZU6	13.02

*Per Pk./25. †Consult Allied.

Crimping Tools

Universal ferrule crimpers crimp insulated and uninsulated ferrules. Front or side conductor entry, positive ratcheting with spring return. Comfort grip plastic handles with hardened steel frames.

Stock No.	Mfr.'s Type	AWG	Wire Entry	Ferrule Size	EACH	
					1-4	5-Up
502-4276	PZU6	26-10	Front	0.14-6 mm ²	223.41	208.52
502-5317	PZU16	8-6	Front	10-16 mm ²	229.50	214.20
502-5318	PZU35	4-2	Side	25 mm ² , 35 mm ²	226.22	211.14
502-5320	PZU50	1	Side	50 mm ²	229.50	214.20



Check Pricing And Availability Of All Items On The Internet At www.alliedelec.com