

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J	ENG. NO.		PIN NO.		DIM. L	DIM. X	DIM. Z	DIM. G TYP BOTH ENDS						J
	A-2220-NA197		43294-0832		(35.05) 1.380	(16.00) .630	(16.13) .635	N/A						
	A-2220-NA502		43294-0833		(35.05) 1.380	(16.00) .630	(16.13) .635	(6.85) .270						
I	A-2220-NAB502		43294-1100		(42.42) 1.670	(16.89) .665	(22.61) .890	(7.62) .300						I
	A-2220-NB197		43294-1147		(44.45) 1.750	(18.24) .718	(23.29) .917	N/A						
H														H
G	A-2220-NA197		A-2220-NA502		A-2220-NAB502		A-2220-NB197							G
	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.						
	09-57-1025	A-2220-2A197	09-78-1021	A-2220-2A502			A-2220-2AB502	09-57-1026	A-2220-2B197					
	09-57-1035	A-2220-3A197	09-78-1031	A-2220-3A502			A-2220-3AB502	09-57-1036	A-2220-3B197					
	09-57-1045	A-2220-4A197	09-78-1041	A-2220-4A502			A-2220-4AB502	09-57-1046	A-2220-4B197					
	09-57-1055	A-2220-5A197	09-78-1051	A-2220-5A502			A-2220-5AB502	09-57-1056	A-2220-5B197					
	09-57-1065	A-2220-6A197	09-78-1061	A-2220-6A502	09-78-1067		A-2220-6AB502	09-57-1066	A-2220-6B197					
F	09-57-1075	A-2220-7A197	09-78-1071	A-2220-7A502			A-2220-7AB502	09-57-1076	A-2220-7B197					F
	09-57-1085	A-2220-8A197	09-78-1081	A-2220-8A502	09-78-1087		A-2220-8AB502	09-57-1086	A-2220-8B197					
	09-57-1095	A-2220-9A197	09-78-1091	A-2220-9A502			A-2220-9AB502	09-57-1096	A-2220-9B197					
	09-57-1105	A-2220-10A197	09-78-1101	A-2220-10A502	09-78-1107		A-2220-10AB502	09-57-1106	A-2220-10B197					
	09-57-1115	A-2220-11A197	09-78-1111	A-2220-11A502			A-2220-11AB502	09-57-1116	A-2220-11B197					
	09-57-1125	A-2220-12A197	09-78-1121	A-2220-12A502	09-78-1127		A-2220-12AB502	09-57-1126	A-2220-12B197					
	09-57-1135	A-2220-13A197	09-78-1131	A-2220-13A502			A-2220-13AB502	09-57-1136	A-2220-13B197					
E	09-57-1145	A-2220-14A197	09-78-1141	A-2220-14A502			A-2220-14AB502	09-57-1146	A-2220-14B197					E
	09-57-1155	A-2220-15A197	09-78-1151	A-2220-15A502	09-78-1157		A-2220-15AB502	09-57-1156	A-2220-15B197					
	09-57-1165	A-2220-16A197	09-78-1161	A-2220-16A502			A-2220-16AB502	09-57-1166	A-2220-16B197					
	09-57-1175	A-2220-17A197	09-78-1171	A-2220-17A502			A-2220-17AB502	09-57-1176	A-2220-17B197					
	09-57-1185	A-2220-18A197	09-78-1181	A-2220-18A502			A-2220-18AB502	09-57-1186	A-2220-18B197					
D														D
C														C
B														B
A														A
ADD PN CHART EC NO: UCP2013-1310 DRWN:MKIPPER 2012/10/02 CHKD:SSOUSEK 2012/10/02 APPR:FSMITH 2012/10/09 DESCRIPTION REV QUALITY SYMBOLS ▽=0 ▽=0 ▽=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM/IN DRAWN BY DATE KSS 1984/10/30 CHECKED BY DATE DMS 1984/10/30 APPROVED BY DATE FSMITH 2012/01/06 MATERIAL NO. SEE CHART SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION SCALE --- INCH DESIGN UNITS INCH THIRD ANGLE PROJECTION WAFER ASSEMBLY CHASSIS MOUNT, KK 2220 SERIES DWG. molex DOCUMENT NO. SDA-2220 SHEET NO. 2 OF 2														
	12	11	10	9	8	7	6	5	4	3	2	1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

09-78-1141