




LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	0	REV PER EC-0S14-0496-04		01FEB2005	GA	GM

1. FOR USE WITH AMP PRO-CRIMPER II HAND TOOL, PART # 354940-1,
OR WITH THE 626 SERIES PNEUMATIC TOOL WITH ADAPTER #679304-1
2. REQUIRES PRO-CRIMPER II DIE SET PART # 58436-1.
FOR CONTACT AND BRAID TERMINATION.



RECOMMENDED STRIP LENGTHS

2	RG-142/U, 142A/U & 142B/U	CONTACT: .068, BRAID: .213	DETAIL C	9-221132-4	415240-2	415233-3	5415232-4			
	CABLE	HEX CRIMP HEIGHTS IN INCHES	STRIP LENGTH	3 FERRULE QTY=1	2 CONTACT QTY=1	1 PLUG ASSY QTY=1	PART NUMBER			
			THIS DRAWING IS A CONTROLLED DOCUMENT.		01FEB2005 G. ATTADIA - DOCK5					
					01FEB2005 J. HAVENER					
					01FEB2005 G. MICHAEL					
					NAME					
					PLUG, N SERIES					
DIMENSIONS: mm [inches]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD						
		0 PLC ± -		PRODUCT SPEC						
		1 PLC ± 0.5 [.02]		—						
		2 PLC ± -		APPLICATION SPEC						
		3 PLC ± -		—						
4 PLC ± -		—			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH		WEIGHT			A2	00779	C=5415232	—
				CUSTOMER DRAWING			SCALE 4:1		SHEET 1 OF 1	REV 0