




SANDVIK BELZER

Double open-end spanner Metric

6M-Set



DIN 3110/ISO 1085

Finish: nickel and chrome-plated, fine-polished.

Material: VANADIUM-EXTRA.

Angle 15°.

Model with extremely flat heads.

In plastic clip.

Set No. 6M/S8 in attractive sales cardboard box.

Product code	EAN code 731415+		No. units	Dim. mm	
6M/8T	1832476	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	735
6M/10T	1832490	1	10	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27 30x32	1570
6M/12T	1832506	1	12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	2070
6M/S8	1832483	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	735
6M-DIN/ISO/8T	1838096	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x21 19x22	735

6M-BOX

Packed in laquered, metal box (320x115x70 mm).

Spanners arranged and protected against humidity and dust.



Product code	EAN code 731415+		No. units	Dim. mm	
6M-BOX	1832513	1	12	6x7, 8x9, 10x11, 12x13, 14x15 16x17, 18x19, 20x22, 21x23 24x26, 27x30, 30x32	2965
Empty metal box					
6M-BOX-L	1835941	1		320x115x70	1410