


### Specifications



|                                                                    |                           |                           |
|--------------------------------------------------------------------|---------------------------|---------------------------|
| Type : Nickel-Metal Hydride Battery                                |                           | Size : 4/5A               |
| Capacity <sup>1)</sup>                                             | Typical                   | 2150mAh                   |
|                                                                    | Minimum                   | 1950mAh                   |
| Nominal Voltage                                                    |                           | 1.2V                      |
| Charging Current x Time                                            | Fast Charge <sup>2)</sup> | 2150 mA x about 1.1h      |
| Ambient Temp.                                                      | Charge Condition          | Fast Charge <sup>2)</sup> |
|                                                                    | 0°C - 40°C                |                           |
|                                                                    | Discharge Condition       |                           |
|                                                                    | 0°C - 50°C                |                           |
|                                                                    | Storage Condition         |                           |
|                                                                    | Less than 30days          | -20°C - 50°C              |
|                                                                    | Less than 90days          | -20°C - 40°C              |
|                                                                    | Less than 1year           | -20°C - 30°C              |
| Internal Impedance <sup>3)</sup><br>(after discharge to E.V.=1.0V) |                           | Approx. 25mΩ(at 1000Hz)   |
| Weight <sup>4)</sup>                                               |                           | Approx. 35 g              |
| Size <sup>4)</sup> : (Diameter) x (Height)                         |                           | 17.0(D) x 43.0(H) mm      |

1) Single cell capacity under the following condition.

Charge : 215mA×16h, Discharge : 430mA(E.V.=1.0V) at 20°C


2) Use recommended charging system.

3) After a few charge and discharge cycles under the above 1) condition.

4) With tube.

### Typical Characteristics

#### Charge



#### Discharge

