

ACCESSORIES

ACCESSORIES

Filter Assembly (Whisper XL DC, Muffin XL DC, Whisper, Whisper XL, Muffin, Muffin XL)

Part No. 551590



Consists of:

551463 Filter Frame




551494 Filter Element

551453 Mounting Brackets

Recommended cut-out 5.5" x 5.16"



ABOVE HARDWARE SUPPLIED




Note: Filters reduce airflow; i.e. a MX2A3's airflow would be reduced to about 87 CFM with P/N 551590 on fan's inlet at 115VAC, 60 Hz.

TOLERANCE: $\pm .015$ (0.38) ON ALL LINEAR DIMENSIONS

Filter Guard Assembly (Flight 60)

Part No. 557239

30 PPI* Replacement Filter Element
Part No. 557241 (pack of 5)
Also available with 45 PPI Filter
Part No. 557240
45 PPI Replacement Filter Element
Part No. 557242 (pack of 5)
Retainer and guard UL94V-0 plastic
Filter element (media) polyurethane foam




Note: Filters reduce airflow
* PPI denotes "pores per inch"

Filter Guard Assembly (Flight 80, Sprint DC, Sprite DC, Sprite)

Part No. 554141

30 PPI* Replacement Filter Element
Part No. 554139 (Pack of 5)
Also available with 45 PPI Filter
Part No. 554142
45 PPI Replacement Filter Element
Part No. 554140 (Pack of 5)
Retainer and guard UL94V-0 plastic
Replacement filter element (media)
polyurethane foam




Note: Filters reduce airflow; i.e. a ST12A3's airflow would be reduced to about 25 CFM with P/N 554141 on fan's inlet at 12VDC.

*PPI denotes "pores per inch"

TOLERANCE B

Part No. 557218



Note: Filters reduce airflow
* PPI denotes "pores per inch"

Part No. 554148



Note: Filters reduce airflow; i.e. a MX2A3's airflow would be reduced to about 75 CFM with P/N 554148 on fan's inlet at 115VAC, 60 Hz. P/N 554149 would reduce airflow to about 68 CFM.

*PPI denotes "pores per inch"

Part No. 477712

Consists of:

- 476000 Filter Frame
- 271018 Washable Filter Element
- 271016 Mounting Clip (2)

Installation Instructions




Note: Filters reduce airflow; i.e. MX2A3's airflow would be reduced into about 82 CFM with P/N 477712 on fan's inlet at 115VAC, 60 Hz (UP).

TOLERANCE A (see page 105)

Part No. 478031


Consists of:
476015 Grille (Spiral)
271016 Mounting Clip (2)
Installation Instructions




TOI FRANCE: + 015 (0.38) ON ALL LINEAR DIMENSIONS

Part No. 477727

Expanded aluminum mesh - snaps onto fan venturi with use of Part No. 271016 mounting clips. (2 REQ'D)




Screen Guard (Flight 120, Muffin DC, Whisper XL DC, Muffin XL DC, Whisper, Whisper XL, Muffin, Muffin XL)
Part No. 550214



Finger Guard (Flight 60)


Part No. 572621

Steel wire, .062 dia., welded and nickel chrome finish
meets UL, CSA .250/6.35 spacing

TOLERANCE B

Finger Guard (Flight 80, Sprint DC, Sprite DC, Sprite)

Part No. 476143




TOLERANCE B

Finger Guard (Flight 80, Sprint DC, Sprite DC, Sprite)

Part No. 550648

Meets UL, CSA .250/6.35 spacing




Color: Black

TOLERANCE A

Finger Guard (Flight 90)

Part No. 554172


Steel wire, .062 dia., welded and nickel chrome finish
Meets UL, CSA .250/6.35 spacing

TOLERANCE B

Finger Guard (Flight 120, Muffin DC, Whisper XL DC, Muffin XL DC, Muffin AC, Whisper, Whisper XL, Muffin, Muffin XL, Skeleton)

Part No. 551147

Meets UL, CSA .250/6.35 spacing




Color: Black

TOLERANCE A

Finger Guard (Flight 120, Muffin DC, Whisper XL DC, Muffin XL DC, Muffin AC, Whisper, Whisper XL, Muffin, Muffin XL, Skeleton)

Part No. 476042

Steel wire, welded and bright zinc plated




TOLERANCE B

Finger Guard (Flight 120, Muffin DC, Whisper XL DC, Muffin XL DC, Muffin AC, Whisper, Whisper XL, Muffin, Muffin XL, Skeleton)

Part No. 550481

Meets UL, CSA .250/6.35 spacing




Color: Black

TOLERANCE A

Finger Guard (Flight 120, Muffin DC, Whisper XL DC, Muffin XL DC, Muffin AC, Whisper, Whisper XL, Muffin, Muffin XL, Skeleton)


Part No. 552934 Meets UL, CSA .250/6.35 spacing

Material: Center Disc: .03 (0.76) THK. C.R.S.
Wire Rings: .062 (1.57) DIA. STEEL
Supports: .080 (2.03) DIA. STEEL
Finish: Bright Zinc Plate with Chromate Treatment

TOLERANCE B

Finger Guard (Galaxy)

Part No. 557216

Made of steel wire finished in bright zinc
Meets UL, CSA .25 dia. spacing


TOLERANCE B

Finger Guard (Galaxy)

Part No. 550651

Material: RTP 305 glass reinforced polycarbonate or
GE Valox 420 polyester

UL Rating 94V-0




Color: Black

TOLERANCE A

Finger Guard (Patriot DC, Patriot)

Part No. 551199

Steel wire, welded and bright zinc plated.
Meets UL, CSA .250/6.35 spacing


TOLERANCE B

Finger Guard (Major DC, Major)

Part No. 550272

Steel wire, welded and bright zinc plated

Meets UL, CSA .250/6.35 spacing




TOLERANCE B

Finger Guard (Biscuit DC, Biscuit)

Part No. 477626

.030 (.76) thick type 302 stainless steel. Screws onto outlet of blower with (2) 8-32 machine screws (not supplied)




TOLERANCE A

Finger Guard (Tarzan)

Part No. 476136

Made of steel wire finished in nickel chrome




TOLERANCE B (see below)

Finger Guard (Caravel)

Part No. 476323

Made of steel wire finished in bright zinc. Mounts using #8 machine screws in the 4 legs equally spaced on 9.688 (246.1) dia.




Note: Also available meeting UL .250 spacing. Call factory for specifications on P/N 557923

TOLERANCE B (see below)

Mounting Clips (Whisper XL DC, Muffin XL DC, Whisper XL, Muffin XL)

Part No. 550113 *Galaxy*

Fits over mounting boss of above fans




5 in./lb. max torque.

Material: .017 (.43) thick tempered spring steel
Finish: Black phosphate

TOLERANCE B (see below)

Plug & Cord

Part No. 550440




UL File No. E42397
GUIDE ZPPW2 Wiring Harness
CSA File No. LR45371

TOLERANCE A (see below)

Mounting Clips (Major DC, Patriot DC, Whisper, Muffin, Major, Patriot)

Part No. 477663 (Flush)
477670 (Standoff)

Fits over .25/.635 mounting flanges of above fans




5 in./lb. max torque.

Material: .017 (.43) thick tempered spring steel
Finish: Black phosphate

TOLERANCE B (see below)

Plug & Cord


Part No. 571064



TOLERANCE B

Plug & Cord

Part No. 428056



UL File No. E42397
GUIDE ZPPW2 Wiring Harness
CSA File No. LR45371

TOLERANCE B

TOLERANCE A: .XX = $\pm .03$ (0.8)
.XXX = $\pm .010$ (0.25)
TOLERANCE B: .XX = $\pm .05$ (1.3)
.XXX = $\pm .015$ (0.38)