

DATE	SYM	REVISION RECORD	DWN.	CK.
10/04	A	ECO No.438	JPM	

DESCRIPTION: SPST SURFACE MOUNT TACT SWITCH
WITH 4/6 NYLON MATERIALS, STAINLESS STEEL
CONTACT AND AVAILABLE WITH TAPE & REEL
PACKAGING (IF SPECIFIED)


SPECIFICATIONS:

RATING: 50 mA @ 12V DC
CONTACT RESISTANCE: 100 mohms MAX.
TRAVEL: .053 [0.25]±.021 [0.10]
LIFE: 1,000,000 CYCLES MIN.
OPERATING FORCE: 160±50gf


NOTES:

- 1. TO SPECIFY TAPE & REEL PACKAGING, ADD TR TO MODEL NO. EXAMPLE: MJTP1138ALT
- 2. TAPE & REEL PACKAGING HOLDS 1250 PIECES PER REEL

MODEL	L
MJTP1138L	.169 [4.30]
MJTP1138AL	.197 [5.00]
MJTP1138BL	.374 [9.50]
MJTP1138CL	.315 [8.00]
MJTP1138EL	.287 [7.30]
MJTP1138FL	.335 [8.50]
MJTP1138GL	.276 [7.00]



UNLESS OTHERWISE SPECIFIED
P.C. TOLERANCES ARE ±.002 [0.05]



Q.A. INSPECT. △ DESIGNATES CRITICAL DIMENSION		WAKEFIELD, MA.	
TOLERANCES (EXCEPT AS NOTED)		DECIMAL ± .012 [0.30]	SCALE 5:1
FRACTIONAL ± —		INCH (MM)	DRAWN APPROVED
ANGULAR ± —		TITLE MJTP1138*L	DATE 04/01/99
APEM CONFIDENTIAL THIS DOCUMENT CONTAINS INFORMATION WHICH IS THE EXCLUSIVE PROPERTY OF APEM COMPONENTS, INC. DISTRIBUTION, REPRODUCTION OR USE BY OTHERS IS NOT PERMITTED WITHOUT THE EXPRESS WRITTEN CONSENT OF APEM COMPONENTS, INC.		DRAWING NUMBER B7392	REV A

