

1

2

3

4

A

B

C


D

A

B

C

D





PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C4GV00	D09P91C6GV00
15	39.14	33.32	25.18	25.12	19.18	D15P91C4GV00	D15P91C6GV00
25	53.03	47.04	39.12	38.84	33.12	D25P91C4GV00	D25P91C6GV00
37	69.32	63.50	55.68	55.30	49.68	D37P91C4GV00	D37P91C6GV00
						200 Matings	500 Matings

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C4GV00LF	D09P91C6GV00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C4GV00LF	D15P91C6GV00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C4GV00LF	D25P91C6GV00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C4GV00LF	D37P91C6GV00LF
						200 Matings	500 Matings



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PESSON	1995/08/25	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1995/08/25			0.XX	±0.1				
Chr	NIRMAL GEORGE	2010/12/11			0.XXX	±0.1		ECN I11-0062		
Appr	SUDHIR VARMA	2010/12/11	Product family			D-SUB	Spec ref -			
		title MALE DELTA D CONNECTOR EUROPE straight press fit				dwg no C01-8646-0360			Rev. F	
		catalog no				-			CUSTOMER sheet 1 of 1	

rev	ecn no	dr	date
B	-	PES	1996/07/24
C	LS05-004	MPE	2005/02/10
D	LS06-0097	LGO	2006/07/29
E	LS06-0186	LGO	2006/07/29
F	I11-0062	RPK	2011/04/05
-	-	-	-
-	-	-	-

REV F - 2006-04-17

1

2

3

4

PDM: Rev:F

STATUS: Released

Printed: Oct 11, 2011



Copyright FCI.