



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT MATERIAL: SILVER OVER COPPER ALLOY
6. OPERATING FORCE: 425 ± 100 CM/STANDARD
7. OPERATING TEMP: -30° to 85°C
8. CIRCUIT SP: 7 POSITIONS, 30° INDEX.
9. DIELECTRIC STRENGTH: 1000V RMS min.@SEA LEVEL.
10. DESIGNATE MAJOR DIMENSIONS
11. SUPPLIED STOP RING, LOCK NUT AND WASHER (NOT SHOWN).





CONTACT CONFIGURATION

Timing: Non-Shorting (BBM)



RECOMMENDED P.C.B. LAYOUT



E-SWITCH®				TITLE			
B	12422	REV. PER NEW CATALOG	CJB	10/28/02	SCALE	DATE	DR
A	11275	RELEASED FOR PRODUCTION	RJC	3/6/01	1.5:1	3/5/01	RJC
REV.	ECN No.	DESCRIPTION	DATE	CHKD			DWG
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND ITS NOT TO BE COPIED OR TRANSFERRED							REV
							B