

ExStik[®] Waterproof Chlorine Meter



Direct reading of Total Chlorine down to 0.01ppm
Unaffected by color/turbidity of the sample

Features:

- Direct reading of Total Chlorine provides fast and easy measurements (less than 2 minutes)
- Low detection limit down to 0.01ppm
- Wide dynamic range of measurement up to 10ppm (use dilution method for 10 to 50ppm)
- Unaffected by sample color or turbidity
- Automatic electronic calibration
- Memory stores, tags and recalls up to 15 readings
- Unique flat surface chlorine electrode
- Waterproof to IP67 standard
- The state of the art LCD simultaneously displays ppm of Total Chlorine and Temperature plus analog bargraph indicator
- Complete with meter and flat surface Chlorine electrode, ExTab[®] reagent tablets (50 tests), protective sensor cap, sample cup with cap, four 3V CR-2032 batteries, and 48" (1.2m) neckstrap



Patent Pending



Testing Chlorine level in public reservoir

ExTab[™] Chlorine Reagent tablets

3 (20mL) ampules of Chlorine Standard

Ordering Information:

CL200	ExStik [®] Chlorine Meter
CL203	ExTabs [™] Reagent tablets (10pk - 100 tests)
CL204	ExTabs [™] Reagent tablets (100pk - 1000 tests)
EX006	Weighted base with 5 solution cups
EX007	Spare sample solution cups (24pk)
CL205	Spare Chlorine electrode
PH105	Spare pH electrode
RE305	Spare ORP electrode
CA903	Carrying case for ExStik [®] kit
CL207	Chlorine standard (1ppm) - 3 ampules (20 mL each)
CA895	Carrying Case, Small with Belt Loop
EX010	Extension Cable, 3ft (1 Meter) with probe weight for ExStik
EX050	Extension Cable, 16ft (5 Meters) with probe weight for ExStik
PH115	Spare Probe. pH, Refillable Reference
RE305	Spare Probe, ORP
EX800	ExStik 3-in-1 Kit (Chlorine, pH, Temp)
EX900	ExStik 4-in-1 Kit (Chlorine, pH, ORP, Temp)

Specifications	
ppm	0.01 to 10.00ppm (10 to 50ppm using dilution method)
Temperature	23° to 194°F (-5 to 90°C)
Resolution	0.01ppm ; 0.1°F/°C
Accuracy	±10% of reading ±0.01ppm; ±1.8°F/±1°C
Power	four SR44W button batteries
Dimensions/Weight	1.4 x 6.8 x 1.6" (35.6 x 172.7 x 40.6mm)/ 3.85oz (110g)

