



AVEN

*High Performance Precision Tools and Optical Inspection Systems
for Industrial, Scientific and Research Applications*

[Home](#) | [My Account](#) | [Sh](#)

[Catalogs & Sales Info](#)

[All Products Listing](#)

[Find A Distributor](#)

[Find A Sales Rep](#)

Wednesday, January 21st, 2009

Come and see Aven at MDM West, February 10-12, 2009 at the Ana

TRR-5000 Niptec Cutter, AWG 24 Steel Wire



[larger image](#)

- Manufactured from Carbon alloy steel and heat treated to optimum hardness
- Anti-glare finish
- Smooth cutting action due to specially designed return spring
- 5000 Series cutters are manufactured with 5MM thick steel which are highly durable and long lasting
- Semi Flush Cutting Blades
- Cutting Capacity 0.5mm (24 AWG) Steel Wire, 10 AWG Copper Wire
- ESD Safe Blades

Model: 10504
Shipping Weight: 0.15lbs

Add to Cart:

[Add to Cart](#)

Customers who bought this product also purchased...



[Solder Utility Tweezers, Curved
Tips, Finger Serrations](#)



[Toothed Tissue Forceps](#)



[General Purpose Tweezers](#)



[College Forceps with Alignment Pin, Curved Serrated Tips 6"](#)



[General Purpose Tweezers, Offset Spade Tips, Smooth](#)