

General Information

Extended Product Type:	M10/10
Product ID:	1SNA115120R1700
EAN:	3472591151206
Catalog Description:	M10/10
Long Description:	M10/10 Screw Clamp Terminal Blocks Feed-through

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

Ordering

EAN:	3472591151206
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	18 g
---------------------	------

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	101 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	0.9 kg
Package Level 1 EAN:	3472591151206
Package Level 2 Units:	500 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	9.35 kg
Product Packing Type:	Box

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Additional Information

Color:	grey
Connection Type:	Screw clamp
Dielectric Test Voltage:	3500 V
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Pollution Degree:	3
Product Main Type:	M10/10
Product Name:	Terminal block
Rated Cross-Section:	10 mm ²
Rated Impulse Withstand Voltage (U _{imp}):	8 kV
Recommended Screw Driver:	5.5 mm
Spacing:	10 mm
Sub-Function:	2 connections
Tightening Torques:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m
Wire Stripping Length:	12 mm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1000
GOST Certificate:	1SND161005A1103

Classifications

E-nummer:	2925512
Object Classification Code:	X

