

181-15302

Slotted Wall Wiring Duct, 1.5" X 3", Non-Adhesive, PVC, Gray, 30ft/Box

Article Number: 181-15302

Part Number: 181-15302

Type: SL1.5X3

[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

[!\[\]\(3342c215b2a8b663596a81468d5dc314_img.jpg\) \[!\\[\\]\\(5e22d44aef1f9548ca8274cbfb388e9d_img.jpg\\) \\[!\\\[\\\]\\\(b011182daf5a0527ed818f91dc4cf8f7_img.jpg\\\) | \\\[!\\\\[\\\\]\\\\(e021942709a217cfed2f781c62feb09c_img.jpg\\\\) Share\\\]\\\(#\\\)\\]\\(#\\)\]\(#\)](#)

Base Data

Part No.	181-15302
Type	SL1.5X3
Color	Gray (GY)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Product Dimensions

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	1.52"
Width (W)	38.61mm
Width (W2)	1.5" / 38.1mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	2.6" / 66.0mm
Height (H)	3.06" / 77.72mm
Mounting Hole Centers	4.00" / 101.60mm

Material and Specifications

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	UL / CSA
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes / Yes

Logistic and Packaging

Packaging Type	box
----------------	-----

Pkg. Qty.	30 / 9.14m
Carton Qty.	120
UPC	089306291923

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

[Home](#) | [About HellermannTyton](#) | [Products](#) | [Careers](#) | [Contact](#) | [Terms](#)

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512