

Product Description



Application range

- For safe sealing of housing against oil, dust and water. For connection thread of a gland or similar parts.

Note

- For optimum sealing of the converter SKINDICHT® ZSE-M12/16/20 x 1.5, we recommend our O-rings with thickness 1.5 mm.
- Delivery will be in max. possible packing unit, minimum order quantity is one packing unit

Technical Data
Colour delivered

Black

Range of temperature

-30°C up to +100°C

Material

NBR Ozone- and UV-resistant

Article List

Part number	Part designation / size	Inner Ø in mm	Cable thickness mm	Pieces / PU
SKINDICHT® O-Ring Perbunan®				
53102000	O M 12 x 2,0	9	2	100
53102001	O M 12 x 1,5	9	1.5	100
53102010	O M 16 x 2,0	13	2	100
53102020	O M 20 x 2,0	17	2	100
53102021	O M 20 x 1,5	17	1.5	100
53102030	O M 25 x 2,0	22	2	100
53102040	O M 32 x 2,0	28	2	50
53102050	O M 40 x 2,0	36	2	50
53102060	O M 50 x 2,0	46	2	25
53102070	O M 63 x 2,0	57	2	25

Footnote:

Perbunan® is a registered trademark of BAYER AG

Photographs are not to scale and do not represent detailed images of the respective products.