



Pinched End Caps 3:1 with inner adhesive


• PEC

Features and Benefits

The PEC-Series can be applied fast and easy like a standard heat shrink tube. The inner adhesive layer and the adhesive plug provide a good and secure water protection. The optimal shrink ratio of 3:1 and different diameters allow a wide range of application. Other diameters and lengths are available on request.


Application

Pinched End Caps can be used for mechanical and environmental protection of stub splices in electrical harnesses. Due to the fast and easy installation, these caps can be used for non-electrical applications as well.



The appropriate end cap for every cable diameter, and cable types.

Material Data	
Material	Polyolefin, cross-linked (POX)
Colour	Black (BK)
Shrink Ratio	3:1
Minimum Shrink Temperature	+120 °C
Operating Temperature	-45 °C to +125 °C
Dielectric Strength	15 kV/mm according to IEC 60684 P2
Flammability	self extinguishing in 30 seconds according to SAE-AMS-DTL-23053/4



PEC-Series expanded



PEC-Series recovered

Technical Table						
Article-No.	Type	Supplied Ø D	Recov. Ø d	Wall (WT)	Length (L)	Length (L2)
416-00000	PEC-3/1	3.0	1.0	1.0	25.0	20.0
416-00003	PEC-4.8/1.5	4.8	1.5	1.0	30.0	25.0
416-00001	PEC-6/2	6.0	2.0	1.0	30.0	25.0
416-00002	PEC-9/3	9.0	3.0	1.4	35.0	27.0

All dimensions in mm. Subject to technical changes.