







# Phone Jack

161-3504

KOBI CONN

Phone Jack



Dimensions: In.

## SPECIFICATIONS

<b>Type:</b>	PCB Mount, Hi-Rel, 2-SPST, N/C Switch
<b>Contact Resistance:</b>	30mΩ max.
<b>Insulation Resistance:</b>	50MΩ min. @ 100VDC
<b>Withstand Voltage:</b>	250VAC for 1 Minute
<b>Operating Temperature:</b>	-10°C ~ +70°C
<b>Flammability:</b>	230°C (3 Seconds)
<b>Housing:</b>	Noryl
<b>Bushing:</b>	Nickel Plated Brass
<b>Terminals:</b>	Nickel Plated Phosphor Bronze
<b>Mounting Hole:</b>	.250"

Date Last Revised: 10-15-05

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300484

161-3504

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3504](#)