








Rating	400mA 32VAC 125mA 125VAC 100mA 50VDC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		A
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1minute		AL
Operation Temperature	-25°C~85°C		
Function	SEE CHART	Thickness:1.5~4.0mm	LED Rating:②20mA,If=2.0VDC



Frame: Black, Nylon 66(94-v2)
Actuator: Red, Nylon 66(94-v2)
Base: Black, PBT(94-V0)
Terminals: Gold plated, Copper
Waterproof: IP67



Illuminated Switch



FUNCTION	TERMINAL
A	0 5 50
(ON) (OFF) 2P SPST	
AL	
(ON) (OFF) 2P SPST (LED)	

() = Momentary Function

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 1/05/11

Rev. 0

Unit: mm

Checked By: G.GULD

Title:
PUSH BUTTON SWITCH

CW P/N:
GPB556XSERIES