






Female connectors, angled


Identification	No. of contacts	Contact length [mm] termination side	Part number	
Type B19 VME, Position P0	95	3.4	17 25 095 1101 17 25 095 2101	
Type B19 with upper shield CompactPCI, Position J3 – VME, Position P0	95	3.4	17 25 095 1102 17 25 095 2102	
Lower shield for type B19 connectors			17 25 000 4102	
Type B22	110	3.4	17 24 110 1101 17 24 110 2101	
Type B22 with upper shield CompactPCI, Positions J2, J5	110	3.4	17 24 110 1102 17 24 110 2102	
Lower shield for type B22 connectors			17 24 000 4102	
Type B25	125	3.4	17 22 125 1101 17 22 125 2101	
Type B25 with upper shield	125	3.4	17 22 125 1102 17 22 125 2102	
Lower shield for type B25 connectors			17 22 000 4102	

Contact positions	X ₁	X ₂
19	37.9	18 x 2 (= 36)
22	43.9	21 x 2 (= 42)
25	49.9	24 x 2 (= 48)

Dimensions [mm]



Board drillings



Board drillings

