









注記

- △ □ 面から2mmの範囲で測定
- 2 嵌合相手ハウジング型 179679, 179680, 179681
- 3 適用製品規格番号: 108-5441
- 4 推奨取付ねじ: JIS B1115, B1122 タップねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク: 0.4N.m (4Kg-cm) 以下)

NOTES

- △ MUST BE KEPT BETWEEN □ AND 2
- 2 THE MATING PLUG HSG. PART NUMBER; 179679, 179680, 179681
- 3 APPLICABLE PRODUCT SPEC NO. 108-5441
- 4 RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH (MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 0.4N.m (4Kg-cm) MAX.)



Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				GRAY 灰色		900429-6
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				HOUSING COLOR ハウジング色		P/N
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				AMP		日本エー・エム・ピー株式会社 Tokyo, Japan
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				名称 (NAME) 88Pos. CAP HOUSING ASS'Y .040II/.070II HD HYBRID I/O CONN		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				88極 キャップ ハウジング アッセンブリ		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				.040II/.070II HD ハイブリッド I/O コネクタ		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				一般公差 (GENERAL TOLERANCE)		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				10mm以下: ±0.2		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				10mm以上, 30mm以下: ±0.25		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				30mm以上, 100mm以下: ±0.3		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				角 度: ±3°		
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				C J		番号 (No.) C-900429
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				尺 度 (SCALE) 1-1		REV. A
Copyright ©1996 AMP (Japan) LTD. ALL RIGHTS RESERVED.				SHEET 1 OF 1		