

SHC1023 -- Cord Connectors




Machined
Aluminum

Hubbell offers a full line of machined aluminum cord connectors in N.P.T. hub sizes ¼" through 1" and cast aluminum 1" to 3". They provide durable performance and a clean attractive look without adding unwanted weight.

Product Specifications

Product Type	Cord Connectors
Material/Style	Aluminum
Cord Diameter Range	.38" - .50" (9.7-12.7)
Cord Connector Body Style	Straight Male
Form Size	F2
HUB Size	1/2"
Color Code	Blue
Effective Operating Temperature	-30°F to +225°F (34°C to +107°C)
Recommended Knockout Hole Size	.86" - .91" (21.8-23.0)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A	1.13" (28.7) Dia.
Dimension B	1.10" (27.9) Ref.
Dimension C	.55" (14.0)
Dimension D	.64" (16.3) Throat Dia.
Dimension E A/C	1.11" (28.2)
Dimension E A/F	1.00" (25.4)

Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page T76
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-T
UPC Number	78358520023
Weight in LBs	0.2



Hubbell Incorporated (Delaware)
 185 Plains Road
 Milford, CT 06460-2420
 Ph: (203) 882-4800
 Fax: (800) 255-1031

