

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200270131

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 0.25mm² PVC Cable, 10.0m (32.81') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

120027

Nano-Change (M8)

Pigtail

IP67

Copper Alloy

Brad Nano-Change (M8) Products

Nano-Change (M8)

N/A

Europe

Single Ended

883906026363

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - O-Ring

Material - Plating Mating

Net Weight

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

5.08mm (.200")

10.0m (32.81')

Black

Threaded

Female-Pigtail

Single

No

PVC

PUR

Nickel-plated Brass

Fluoro-elastomer

Gold

310.224/g

Straight to Pigtail

4

-25°C to +80°C

N/A

UL 2464

Electrical

Current - Maximum per Contact

Voltage - Maximum

3.0A

60V

Material Info

Engineering Number

404000E02M100

Reference - Drawing Numbers

Sales Drawing

1200860594-000



EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120027 Series

This document was generated on 07/31/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION