

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

MOLDED CHOKES (MCGS TYPE)

PRODUCT IDENTIFICATION (產品識別)

MCGS □ □ - □ □ □ □

Jameco Part Number 372373

1 2 3 4 5

(1) MOLDED CHOKES TYPE (MCGS 壓模線圈型)

(2) B: In Bulk(散裝)

A: Tapping with Ammo Box(盒裝)


R: Tapping with Reel(捲裝)

(3) Type 型式(1302,1303,1304,1309,1310,1501)

(4) Inductance(電感值)

(5) Tolerance (誤差值) (J 5%,K 10%,M 20%)

CONFIGURATIONS & DIMENSIONS (結構圖及規格尺寸)



TYPE(型式)	∅A	B	C	∅D
MCGS 1302	4.83 ± 0.25	11.18 ± 0.25	25.91 (min)	0.635 ± 0.05
MCGS 1303	2.41 ± 0.25	6.35 ± 0.25	25.91 (min)	0.500 ± 0.05
MCGS 1304	3.96 ± 0.25	9.53 ± 0.25	25.91 (min)	0.600 ± 0.05
MCGS 1309	6.50 ± 0.10	14.50 ± 0.25	25.91 (min)	0.800 ± 0.05
MCGS 1310	1.98 ± 0.25	5.08 ± 0.25	25.91 (min)	0.410 ± 0.05
MCGS 1501	4.11 ± 0.25	10.41 ± 0.25	25.91 (min)	0.600 ± 0.05

INDUCTANCE & RATED CURRENT RANGES (電感及定格電流範圍)

TYPE (型式)	INDUCTANCE (電感值)	RATED CURRENT (定格電流)
MCGS 1302	0.15..... 1000 uH	3050 78 mA (MAX)
MCGS 1303	0.10..... 1000 uH	1380 28 mA (MAX)
MCGS 1304	0.15..... 1000 uH	2740 82 mA (MAX)
MCGS 1309	0.10..... 1000 uH	1900 80 mA (MAX)
MCGS 1310	0.10..... 270 uH	895 39 mA (MAX)
MCGS 1501	0.10..... 10000 uH	1790 24 mA (MAX)

MOLDED CHOKES (MCGS TYPE)

ELECTRICAL CHARACTERISTICS FOR MCGS 1303 SERIES(MCGS 1303 系列電子特性規格)

PART NUMBER 產品料號	INDUC - TANCE 電感值(L)	Q(min) 品質因數	F (MHZ) 測試頻率	SRF(MHZ) (min) 共振頻率	RDC(Ω) (max) 直流阻抗	IDC(mA) (max) 定格電流
MCGS 1303-R10	0.10 uH	40	25	680	0.08	1380
MCGS 1303-R12	0.12 uH	40	25	640	0.09	1300
MCGS 1303-R15	0.15 uH	38	25	600	0.10	1230
MCGS 1303-R18	0.18 uH	35	25	550	0.12	1120
MCGS 1303-R22	0.22 uH	33	25	510	0.14	1040
MCGS 1303-R27	0.27 uH	33	25	430	0.16	975
MCGS 1303-R33	0.33 uH	30	25	410	0.22	830
MCGS 1303-R39	0.39 uH	30	25	365	0.30	710
MCGS 1303-R47	0.47 uH	30	25	330	0.35	660
MCGS 1303-R56	0.56 uH	30	25	300	0.50	550
MCGS 1303-R68	0.68 uH	28	25	275	0.60	500
MCGS 1303-R82	0.82 uH	28	25	250	0.85	420
MCGS 1303-1R0	1.00 uH	25	25	230	1.00	390
MCGS 1303-1R2	1.20 uH	25	7.9	150	0.18	620
MCGS 1303-1R5	1.50 uH	28	7.9	140	0.22	560
MCGS 1303-1R8	1.80 uH	30	7.9	125	0.30	480
MCGS 1303-2R2	2.20 uH	30	7.9	115	0.40	415
MCGS 1303-2R7	2.70 uH	37	7.9	100	0.55	355
MCGS 1303-3R3	3.30 uH	45	7.9	90	0.85	285
MCGS 1303-3R9	3.90 uH	45	7.9	80	1.00	263
MCGS 1303-4R7	4.70 uH	45	7.9	75	1.20	239
MCGS 1303-5R6	5.60 uH	50	7.9	65	1.80	195
MCGS 1303-6R8	6.80 uH	50	7.9	60	2.00	185
MCGS 1303-8R2	8.20 uH	55	7.9	55	2.70	160
MCGS 1303-100	10.00 uH	55	7.9	50	3.30	144
MCGS 1303-120	12.00 uH	45	2.5	40	2.70	160
MCGS 1303-150	15.00 uH	45	2.5	35	2.80	157
MCGS 1303-180	18.00 uH	50	2.5	30	3.10	149
MCGS 1303-220	22.00 uH	50	2.5	25	3.30	144
MCGS 1303-270	27.00 uH	50	2.5	20	3.50	140
MCGS 1303-330	33.00 uH	45	2.5	24	3.40	130