

■ Magnetic Buzzer

Magnetic Indicator(Internal Circuitry Type)

Pin Type

KXG1612C


■ Shape

KXG1612C



Rated Voltage (VDC)	12
Operating Voltage Range (VDC)	8.0~16.0
Current Consumption (mA)	Max.35
Sound Pressure Level (dBA)	Min.85dBA(Typical 92) @10cm
Rated Frequency (Hz)	Min2200±300
Operating Temperature ()	-20~+60
Storage Temperature ()	-30~+70
Weight (Gram)	7
Material	PPO(Black)

■ Dimension



■ Characteristic / Schematic Diagram

