



Field Interface Modules



Passive - 2 wire
8 Channel
Input/Output
Allen-Bradley



Technical Data

Type	RS PLC DI 8PT AC			RS PLC DI/O 8PT + BUS			RS PLC DI/O 8PT - BUS		
Part number	998011	120 VAC	1771-IA, 1771-IA2	998012	10-27 VDC	1771-IB	998013	12-24 VDC	1771-IV
		24 VAC	1771-ON, 1771-IN		50 VDC	1771-IC		10-27 VDC	1771-OB
		120 VAC	1771-OA		24-48 VDC	1771-IH		42-53 VDC	1771-OC
		120 VAC	1746-IA4, 1746-IA8		12-24 VDC	1771-IT		10-50 VDC	1746-OB8
					5-50 VDC	1746-OV8		24 VDC	1746-IV8
					24 VDC	1746-IB8			
					TTL	1771-OG			
Rated voltage	See Above								
Rated current	3.0 A per channel / 6.0 A per module / 3.0 A per common								
Cable connection	(1) 1 x 20 pin IDC								
LED Indicators	No								
Operating Temperature	0°C...+50°C								
Storage Temperature	-20°C...+60°C								
Dimensions LxWxH mm	75 x 70 x 59								
Terminal Wire Size	#26...14 AWG								
Terminal Type	Screw Clamp								
Approvals									

Wiring Schematics

