



PANDUIT PART NO.	PART DESCRIPTION	MATERIAL	STYLE	"B"	"C"	COLOR (PRINT ON AREA)	LABELS/ROLL
N050X075CBC	18-14 AWG WIRES	GMC4	1	0.50 [12.70]	0.75 [19.05]	WHITE	125
N050X150CBC	CAT. 5e/CAT. 6 CABLE	GMC4	1	0.50 [12.70]	1.50 [38.10]	WHITE	75
N100X125CBC	12-10 AWG WIRES	GMC4	1	1.00 [25.40]	1.25 [31.75]	WHITE	75
N100X150CBC	CAT. 5e/CAT. 6 CABLE	GMC4	2	1.00 [25.40]	1.50 [38.10]	WHITE	75
N100X175CBC	8-4 AWG WIRES	GMC4	1	1.00 [25.40]	1.75 [44.45]	WHITE	50
N050X075C1C	18-14 AWG WIRES	GMC6	2	0.50 [12.70]	0.75 [19.05]	WHITE	125
N050X075C2C	18-14 AWG WIRES	GMC6	2	0.50 [12.70]	0.75 [19.05]	YELLOW	125
N050X125C1C	12-10 AWG WIRES	GMC6	2	0.50 [12.70]	1.25 [31.75]	WHITE	75
N050X125C2C	12-10 AWG WIRES	GMC6	2	0.50 [12.70]	1.25 [31.75]	YELLOW	75
N100X075C1C	18-14 AWG WIRES	GMC6	2	1.00 [25.40]	0.75 [19.05]	WHITE	125
N100X075C2C	18-14 AWG WIRES	GMC6	2	1.00 [25.40]	0.75 [19.05]	YELLOW	125
N100X125C1C	12-10 AWG WIRES	GMC6	2	1.00 [25.40]	1.25 [31.75]	WHITE	75
N100X125C2C	12-10 AWG WIRES	GMC6	2	1.00 [25.40]	1.25 [31.75]	YELLOW	75

NOTES:

1. DIMENSIONS IN []
ARE IN MILLIMETERS.



CAD FILENAME/LAYERS

100743CJ_DC_C10693/13B

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
P1 LABEL CASSETTE
NON-LAMINATED LABEL

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1 (XXX) ± .025
(.XX) ± .030 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

1	6/25/10	RVU		ADD NEW PN N***X***C*C.	6029	R				DRAWN BY RVU	MAT'L:	SCALE NTS
0	4/21/08	RVU		DRAWING RELEASE	5403	R				DATE 4/22/08	SEE TABLE	DRAWING NO. C10693
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D		DWG A SIZE