

Coaxial Cable Connector 11_BNC-50-7-2/133_N

Description

Straight cable plug

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Centre contact soldered
Outer 2contact clamped
Weight 0.0368 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing DOU-00071252
Catalogue drawing DOU-00006636
Assembly instruction DOC-0000179854

Ordering Information

Single package 11_BNC-50-7-2/133_NE

Additional Information

Suitable cables RG_214_/U, RG_225_/U