

UNCONTROLLED DOCUMENT

LX

PART NUMBER

LCD-S3X1C50TR/A

REV.


A

REV. E.C.N. NUMBER AND REVISION COMMENTS


DATE

A E.C.N. #11148.

02.07.07



DIGIT DETAIL



PIN NO.	1	2	3	4	5	6	7	8	9	10
SEGMENT	COM	Y	K	N/C	N/C	N/C	N/C	DP1	1E	1D
PIN NO.	11	12	13	14	15	16	17	18	19	20
SEGMENT	1C	DP2	2E	2D	2C	DP3	3E	3D	3C	3B
PIN NO.	21	22	23	24	25	26	27	28	29	30
SEGMENT	3A	3F	3G	2B	2A	2F	2G	COL	1B	1A
PIN NO.	31	32	33	34	35	36	37	38	39	40
SEGMENT	1F	1G	N/C	N/C	N/C	N/C	OVER	LO	BAT	X
										COM

CHARACTERISTICS

FLUID TYPE:	TN
BACKGROUND COLOR:	GRAY
VIEWING DIRECTION:	6:00
DISPLAY MODE:	REFLECTIVE
OPERATING VOLTAGE:	3.0~5.0 VOLTS A.C.
OPERATING TEMP.	0°C TO 50°C
STORAGE TEMP.	-20°C TO 70°C
DRIVING METHODE:	STATIC
CONNECTION TYPE:	40 PINS

REPLACES PART #: LCD-S50C3X1TR/A

UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), XX=±0.5 (±0.020), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN.= +DECIMAL PRECISION -0.00 MAX.= +0.00 -DECIMAL PRECISION

REV.

A

PART NUMBER

LCD-S3X1C50TR/A

0.50" CHARACTER HEIGHT, 3 1/2 DIGIT LCD GLASS,
TN, REFLECTIVE, 40 PINS.

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



290 E. HELEN ROAD
PALATINE, IL 60067-6976
PHONE: +1.847.359.2790
US WEB: www.lumex.com
TW WEB: www.lumex.com.tw

DRAWN BY:

JC

CHECKED BY:

APPROVED BY:

DATE: 11.19.98

PAGE: 1 OF 1

SCALE: N/A

UNCONTROLLED DOCUMENT