




PM 5.08/90

new





Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	17.5	16	10
Wire size (mm ² /AWG)	1.5	24...14	14

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 50

Solder pin length		3.5 mm	3.5 mm		
Color					
Poles	Type	Part No.	Part No.	Qty.	
2	PM 5.08/2/90	1760490000	1760510000	500	
3	PM 5.08/3/90	1760500000	1760520000	500	
4	PM 5.08/4/90	67600961	67600974		
5	PM 5.08/5/90	67600962	67600975		
6	PM 5.08/6/90	67600963	67600976		
7	PM 5.08/7/90	67600964	67600977		
8	PM 5.08/8/90	67600965	67600978		
9	PM 5.08/9/90	67600966	67600979		
10	PM 5.08/10/90	67600967	67600980		
11	PM 5.08/11/90	67600968	67600981		
12	PM 5.08/12/90	67600969	67600982		
13	PM 5.08/13/90	67600970	67600983		
14	PM 5.08/14/90	67600971	67600984		
15	PM 5.08/15/90	67600972	67600985		
16	PM 5.08/16/90	67600973	67600986		

Accessories	Page
Marking	42
Mounting	-
Miscellaneous	45

MK8 5.08/135



Technical data	VDE	UL	CSA
Rated voltage (V)	60*	150	150
Rated current (A)	16	15	15
Wire size (mm ² /AWG)	1.5	22...12	14

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 51

Solder pin length		5.0 mm		
Color				
Poles	Type	Part No.	Qty.	
2	MK8 5.08/2/135	0332060000	200	
3	MK8 5.08/3/135	0307860000	100	
4	MK8 5.08/4/135	0307760000	100	
10	MK8 5.08/10/135	0302660000	50	

Accessories	Page
Marking	42
Mounting	-
Miscellaneous	45