

6

5

4

3

2

1

MATERIAL AND FINISH:

Insulator: Polycarbonate, UL-94V-0 rated

Contacts: IEC C13, 70°C: Brass

IEC C15, 120°C: Bronze

ELECTRICAL SPECIFICATIONS:




Current rating: 10 A

Voltage rating: 250 VAC

ORDERING CODE:43R01- $\frac{3}{1}$ $\frac{1}{2}$ **1) ELECTRICAL CIRCUIT
CONFIGURATION**1 = IEC C13, 10A 250V 70°C
A DIN 49 4572 = IEC C15, 10A 250V 120°C
D DIN 49 458**2) COLOR**

1 = BLACK


2 = GRAY

**RoHS
COMPLIANT****NOTES:**

1. Contains integral cable clamp strain relief & internal screw type connections. Maximum wire gauge is 16AWG stranded.

2. Recommended screw torque: 1.2Nm

3. Recommended strip length for jacket and conductors:



REV	DATE	CHANGE	CHNG		CHK		APPR
			PB	PB	PB	PB	
A	1/25/07	NOTES 2 & 3; RoHS					
B	6/9/10	ADD C15 CONTACT MATERIAL					

TOLERANCE
UNLESS OTHERWISE SPECIFIED

X ± 1
X.X ± 0.4
X.XX ± 0.20

DRAWN BY	GQ	DATE:	08/20/01
CHECK BY	TD	DATE:	08/22/01
APPR BY	PB	DATE:	08/22/01

Power Dynamics, Inc.

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: IEC 60320 C13 & C15 FEMALE POWER CORD
PLUG; STRAIGHT CONNECTIONPART #: **43R01-X3X1**SIZE: A
SCALE: NTSALL DIMENSIONS FOR REFERENCE ONLY
DIMENSIONS ARE IN MILLIMETERSSHEET
1 of 1REV: **B**