



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



BIT,STEP #14 (PKGD)

Kwik Stepper® Step Bits

Cat No: 36414

UPC No: 783310364146

Description

- Unique split-tip design penetrates through steel faster
- Resists walking or skidding, even on round surfaces
- Balanced, double-flute construction requires less pressure, does the work for you
- Designed and manufactured in USA.

Specifications

- Capacity : Cut Up Through 3/8 IN (9.500 MM) Mild Steel, Copper, Brass,Aluminum, Wood, Plastic and Laminates
- Hole Size : 7/8 IN (22.200 MM), 1-1/8 IN (28.600 MM), 1.201 IN (32.500 MM), 1-7/32 IN (31.000 MM), 1-1/4 IN (31.800 MM), 1-3/8 IN (34.900 MM)
- Maximum Material Thickness : 10 GA (3.500 MM)
- Minimum Chuck Size : 3/8 IN (9.500 MM)
- Overall Length : 3-7/8/ IN (85.700 MM)
- Sub Brand : Kwik Stepper
- Type : Multi Hole