

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Sure drive adjustable wrench
Catalogue number	4365
Date	28/03/2007

Range Description A range of three adjustable wrenches with Sure drive jaw profile				
Features • Sure drive jaw profile that grips bolt heads and nuts at the flanks, not at the corners – eliminates rounding off • Chrome vanadium steel, matt chrome plated – for maximum strength and corrosion protection • Soft grip handle for comfort and grip • 18% wider jaw opening when compared to a standard pattern – more capacity • Lightweight design with narrow jaw for improved access • Metric and imperial graduations to aid pre setting • Clear direction of rotation indication from permanent markings				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4365 200	Sure drive adjustable wrench 200mm – display packed	5013969051629	82042000	3
T4365 250	Sure drive adjustable wrench 250mm – display packed	5013969051636	82042000	3
T4365 300	Sure drive adjustable wrench 300mm – display packed	5013969051643	82042000	3

Technical product information	Recommended nut or bolt head size ranges										
		7	8	10	11	13	17	19	24	30	36
	200mm 8"										
	250mm 10"										
	300mm 12"										
Standards compliance	None applicable										
User health and safety information	None applicable										
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations										
Material safety data	None applicable										
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered										
Country of origin	Taiwan										

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4365 200	60	18	207	249	100	18	280	267
T4365 250	65	20	260	388	110	20	330	409
T4365 300	85	23	310	599	125	23	380	625

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4365 200	110	300	50	880		
T4365 250	125	350	65	1334		
T4365 300	140	400	70	2018		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4365 200	17	Blister	1	Backing card			79	Box
T4365 250	20	Blister	1	Backing card			109	Box
T4365 300	25	Blister	1	Backing card			143	Box