


△ RECOMMENDED SCREW SIZE ; M2.6 PANHEAD SCREW.(L=5)
2 RECOMMENDED P.C BOARD THICKNESS ; 1.6mm±0.15
△ POST PATTERN AS SHOWN ON THIS END FOR ALL POSITION.

LEAD FREE



1.905x3=	PA6T	37.5	10.3	42.8	52.40	42.50	35.48	46.50	30.48	24	50	1-5917738-7
	PA6T	28.61	8.3	33.9	43.51	33.61	26.59	37.61	21.59	17	36	1-5917738-5
	PBT	37.5	10.3	42.8	52.40	42.50	35.48	46.50	30.48	24	50	5917738-7
	PBT	28.61	8.3	33.9	43.51	33.61	26.59	37.61	21.59	17	36	5917738-5
	PBT	22.26	8.3	27.6	37.16	27.26	20.24	31.26	15.24	12	26	5917738-4
OBSOLETED	PBT	18.45	8.3	23.8	33.35	23.45	16.43	27.45	11.43	9	20	5917738-2
OBSOLETED	PBT	14.64	8.3	19.9	29.54	19.64	12.62	23.64	7.62	6	14	5917738-1
	HSG MAT'L	H	G	F	E	D	C	B	A	N	POSITION	PART NO.

TE Connectivity Ltd.

4	NAME 名称
---	------------

CHAMP.050 SERIES (II)			
FMS-TYPE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTION

A2	00779	C-5917738	
----	-------	-----------	--