

Item # B4063, Mobile Load Coil Antennas



[larger image](#)

Stock Locator

- Low loss coil form adds dimensional and frequency stability
- ABS material is injection molded around solid brass inserts to create a virtually indestructible housing that is virtually leak proof
- All silver soldered joints ensure electrically and mechanically secure connections

Specifications

Model	UHF Models
Description	5/8 Wave
Frequency Range	406 - 430 MHz
Center Frequency	Tunable
Gain	3 dB
Overall Length	15.0 inches
Whip Style	13" Straight
Options	Black Chrome Finish Black Shock Spring Shock Spring

Print Back