

PRODUCT NUMBER

XXXXX-YYYHPLF

LEAD FREE OPTION
SEE NOTE 1,13


SPECIAL OPTIONS
SEE NOTE 1 OR 10

HIGH TEMPERATURE PLASTIC
SEE NOTE 1


NO OF
POSITIONS
SEE NOTE 1

PIN PLATING
SEE SHEET 2


BASE PART NO.



TOP VIEW




DETAIL P
SCALE 5:1
TYP BOTH ENDS



SIDE VIEW

END VIEW

NOTE 6



RECOMMENDED HOLE PATTERN

67996-X XX-XXX XXX LF

TAIL LENGTH (EXAMPLE BELOW)
3.0mm=030 12.8mm=128
(SEE NOTE 16 & 17)

MATING LENGTH (EXAMPLE BELOW)
5.0mm=050 25.5mm=255
(SEE NOTE 16 & 17)

TOTAL NUMBER OF POSITIONS
FROM 2 (2X1) THRU 72 (2X36) POS.

PIN PLATING (SEE NOTE 14)
1=0.76µm Au
4= PURE TIN
8=0.36µm Au

BASE PART NO.
DOUBLE ROW

mat'l. code NOTE 2 & 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ISO 1101		product family BERGSTIK	
ltr	ecn no	dr	date	tolerances unless otherwise specified		linear		INCH/MM		title	
DF	N11-0180	J.Z	2011-05-31	angles		.XX±.01/.XX±.3		scale 2:1		BERGSTIK II HEADER D/R	
DG	ELX-N-13471	J.Z	2011-11-16	0°±2°		.XXX±0.005/.XXX±.13		F		.100/2.54cc STRAIGHT	
						.XXX±0.020/.XXX±.051		F		dwg no	
				dr		T.BREWBAKER		12/21/94		sheet 1 of 8	
				enr		T.HANNA		12/21/94		67996	
				chr		J.MURPHY		12/21/94		A3	
				appd		T.HANNA		12/21/94		type	
sheet	revision	DG	...	DG						Product Customer Drawing	
index	sheet	1	...	8							

PDS: Rev :DG

STATUS: Released

Printed: Nov 16, 2012

PIN PLATING CODES:	
XXXX-1YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-2YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-3YY	50u"/1.27u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 15)
XXXX-4YYHLF	
XXXX-5YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-6YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-7YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-8YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-9YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-0YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni

NOTES

1. PART NUMBER OPTIONS:
PIN PLATING CODES (SEE ABOVE)

HIGH TEMPERATURE MATERIAL:

PART NUMBERS WITH AND WITHOUT "H" WILL BE SUPPLIED WITH HIGH TEMPERATURE PLASTIC.

NUMBER OF POSITIONS :

EVEN NUMBER OF POSITIONS FROM 2 (2X1) THROUGH 72 (2X36).
-X00H INDICATES BERGSTRIIP PRODUCT. SEE PAGE 3
FOR SPECIAL GEOMETRY OF THIS CONTINUOUS STRIP PRODUCT.
AUTOMATED REELS WILL CONTAIN 45,000 PINS.
SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

PACKAGING:

PACKAGED IN POLY BAGS.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED
IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "G" ARE PACKAGED
IN GPAX FOR IBM ONLY. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.
PART NUMBERS FOLLOWED BY A "C" ARE PACKAGED IN TUBES
WITH A PICKUP CAP APPLIED.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "A" ARE PACKAGED 
IN TAPE/REEL WITH PICKUP CAP P/N 95730-003 APPLIED, PER BUS-14-345.

LEAD FREE:

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE
OPTION, NOT AVAILABLE FOR -5YY,-5YYH, -6YY & -6YYH




2. BODY MATERIAL:

BODY MATERIAL : MANUFACTURER'S OPTION OF NYLON, PCT GLASS FIBER
REINFORCED OR MINERAL FILLED LCP FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK
BERGSTRIIP™ PRODUCED WITH HIGH TEMPERATURE LCP
THERMOPLASTIC, FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK
PART NUMBERS WITH "H" AND WITHOUT SUFFIX WILL WITHSTAND EXPOSURE
TO 260° C PEAK TEMPERATURE FOR 20 SECONDS IN
WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.


3. PIN MATERIAL: PHOS BRONZE.
4. MEASURED WITH PART IN RESTRAINED CONDITION.
5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.
6. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.
7. MILITARY BERGSTIK HEADER
P/N XXXXX-XY-MIL
NOT AVAILABLE.
8. ±.010/0.25 TOL APPLIES TO ALL "G" TAILS EXCEPT
INDICATED PARTS ON TABLE WHERE +.010/0.25 -.000/0.00
APPLIES.
9. NOTCH CONFIGURATION WILL VARY PER VENDOR'S DISCRETION.
10. BERGSTRIIP™ PART NUMBERS FOLLOWED BY
BY A "B" ARE BULK PRICED.
11. TAIL LENGTH (DIM. G) TO BE ±.008/.020.
12. POSITIONS PER ROW 37 TO 50 CAN BE PRODUCED,
BUT FLATNESS AND CURVATURE MAY NOT BE
HELD AS CLOSE AS 36 POSITIONS.
13. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. PLATING OPTIONS:
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL,
OPTIONALLY (78~295u")/2~7.5u) TIN ON TAIL.
15. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT
ENVIRONMENTS."
16. THE OAL DON'T EXCEED 34.5mm
17. INCREMENTS BY 0.1mm IN LENGTHS ONLY
18. FOR SPECIAL PACKAGING REQUEST PLEASE CONTACT PRODUCT MANAGER FOR AVAILABILITY
19. TO DETERMINE DIMENSIONS:
N=NUMBER OF POSITION PER ROW
EXAMPLE: 10 POS. N X .100/2.54

mat'l. code NOTE 2 & 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family BERGSTIK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 2:1 	title
DG					angles linear XX±01/XX±3 XXX±0.005/XXX±.13 XXXX±.0020/XXX±.05		BERGSTIK II HEADER D/R .100/2.54cc STRAIGHT
					dr T.BREWBAKER 12/21/94 enr T.HANNA 12/21/94 chr J.MURPHY 12/21/94 appd T.HANNA 12/21/94		dwg no sheet 2 of 8 size 67996 A3
sheet index		revision sheet					type Product Customer Drawing

BERGSTRIPTM HEADER



REEL PACKING DIMENSIONS



mat'l. code NOTE 2 & 3				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 	product family BERGSTIK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title	
DG					angles	linear	$.XX \pm .01 / .X \pm .3$ $.XXX \pm 0.005 / .XXX \pm .13$ $.XXXX \pm .0020 / .XXX \pm .05$	INCH/MM	BERGSTIK II HEADER D/R .100/2.54cc STRAIGHT	
					0° ± 2°			scale 2:1	dwg no	
					dr	T.BREWBAKER	12/21/94		sheet 3 of 8	
					enr	T.HANNA	12/21/94		67996	
					chr	J.MURPHY	12/21/94		A3	
					appd	T.HANNA	12/21/94		type Product Customer Drawing	
sheet index	revision sheet									

PRODUCT NUMBER	TOT. PIN	LGTH.	TAIL LENGTH		MATING LENGTH				BERGSTRIPTM	LF OPTION	
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	PACKAGING	NOTES	AVAILABLE		
69132-YYY	0.760	19.30	0.120	3.05	0.540	13.72	POLY BAGS/TUBES	-	NO	NOTE 1,13 	
69133-YYY	0.615	15.62	0.285	7.24	0.230	5.84	POLY BAGS	-	NO		
69157-YYY	0.410	10.41	0.110	2.79	0.200	5.08	POLY BAGS	-	NO		
71217-XXYH	1.000	25.40	0.450	11.43	0.450	11.43	POLY BAGS	-	NO		
71222-XXYH	0.850	21.59	0.250	6.35	0.500	12.70	POLY BAGS	-	NO		
72273-XXYH	0.725	18.42	0.110	2.79	0.515	13.08	POLY BAGS	-	NO		
72448-XXYH	0.658	16.71	0.172	4.37	0.386	9.80	POLY BAGS	-	NO		
72455-XXYH	0.598	15.19	0.180	4.57	0.318	8.08	POLY BAGS	-	NO		
72455-632HG	0.598	15.19	0.180	4.57	0.318	8.08	GPAX	NOTE 1	NO		
73503-XXYH	0.420	10.67	0.120	3.05	0.200	5.08	POLY BAGS	-	NO		
73596-XXYH	0.795	20.19	0.110	2.79	0.585	14.86	POLY BAGS	-	NO		
74317-XXYH	0.532	13.51	0.309	7.85	0.123	3.12	POLY BAGS	NOTE 11	NO		
74318-XXYH	0.592	15.04	0.369	9.37	0.123	3.12	POLY BAGS	NOTE 11	NO		
74999-XXYH	0.508	12.90	0.090	2.29	0.318	8.08	POLY BAGS	-	NO		
78212-YYY	0.710	18.03	0.350	8.89	0.260	6.60	POLY BAGS	-	NO		
78233-YYY	0.568	14.43	0.150	3.81	0.318	8.08	POLY BAGS	-	NO		
78269-YYY	0.385	9.78	0.095	2.41	0.190	4.83	POLY BAGS	-	NO		
78286-YYY	0.500	12.70	0.160	4.06	0.240	6.10	POLY BAGS/TUBES	-	NO		
78932-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
78933-YYY	0.695	17.65	0.285	7.24	0.310	7.87	POLY BAGS	-	NO		
78988-YYY	0.540	13.72	0.135	3.43	0.305	7.75	POLY BAGS	-	NO		
78989-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
78990-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
78991-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
78992-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
78993-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
78994-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		NOTE 1,13

[illegible]

PRODUCT NUMBER	TOT. PIN LGTH.		TAIL LENGTH		MATING LENGTH				BERGSTRIPTM	LF OPTION	
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	PACKAGING	NOTES	AVAILABLE		
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC					
78995-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-	NOTE 1,13	
78996-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
79242-YYY	0.930	23.62	0.340	8.64	0.490	12.45	POLY BAGS	-	NO		
79243-YYY	1.230	31.24	0.390	9.91	0.740	18.80	POLY BAGS	-	NO		
79244-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-		
79268-YYY	1.020	25.91	0.120	3.05	0.800	20.32	POLY BAGS	-	NO		
79271-YYY	1.100	27.94	0.500	12.70	0.500	12.70	POLY BAGS	-	NO		
79425-YYY	0.410	10.41	0.120	3.05	0.190	4.83	POLY BAGS	-	NO		
79821-YYY	0.730	18.54	0.200	5.08	0.430	10.92	POLY BAGS	-	NO		
84610-YYYH	0.380	9.65	0.120	3.05	0.160	4.06	POLY BAGS	-	NO		
84760-YYYH	0.870	22.09	0.150	3.81	0.620	15.74	POLY BAGS	-	NO		
84784-YYYH	1.130	28.70	0.122	3.09	0.908	23.06	POLY BAGS	-	NO		
84934-YYYH	1.375	34.93	0.625	15.88	0.650	16.51	POLY BAGS	-	NO		
84976-YYYH	0.730	18.54	0.400	10.16	0.230	5.84	POLY BAGS	-	NO		
86503-YYY	0.470	11.94	0.120	3.05	0.250	6.35	POLY BAGS	-	NO		
86581-YYY	0.450	11.43	0.120	3.05	0.230	5.84	POLY BAGS	NOTE 8	NO		
86817-YYY	0.925	23.50	0.120	3.05	0.705	17.91	POLY BAGS	-	NO		
86827-YYY	0.700	17.78	0.120	3.05	0.480	12.19	POLY BAGS	-	NO		
86832-YYY	0.525	13.34	0.100	2.54	0.325	8.26	POLY BAGS	-	NO		
86834-YYY	1.335	33.91	0.585	14.86	0.650	16.51	POLY BAGS	-	NO		
86836-YYY	0.870	22.10	0.120	3.05	0.650	16.51	POLY BAGS	-	NO		
86837-YYY	0.600	15.24	0.120	3.05	0.380	9.65	POLY BAGS	-	NO		
87037-YYY	1.240	31.50	0.120	3.05	1.020	25.91	POLY BAGS	-	NO		
87052-YYY	0.990	25.15	0.120	3.05	0.770	19.56	POLY BAGS	-	NO		
87203-YYY	0.545	13.84	0.150	3.81	0.295	7.49	POLY BAGS	-	NO		
87344-YYY	1.375	34.93	0.219	5.56	1.056	26.82	POLY BAGS	-	NO		NOTE 1,13

NOTE 1,13

FCIconnect.com B

C

D

mat'l. code NOTE 2 & 3					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK								
ltr	ecn no	dr	date		tolerances unless otherwise specified							title							
DG					angles	linear	$\pm .01 / \pm .3$					INCH/MM	BERGSTIK II HEADER D/R .100/2.54cc STRAIGHT						
							$\pm .005 / \pm .13$												
							$0^\circ \pm 2'$ $\pm .0020 / \pm .051$												
					dr	T.BREWBAKER	12/21/94					FCI 		dwg no 67996	sheet 6 of 8 A3	size			
					engr	T.HANNA	12/21/94												
					chr	J.MURPHY	12/21/94												
					appd	T.HANNA	12/21/94												
sheet index		revision sheet																	

1

2

3

4

5

6

PRODUCT NUMBER	TOT. PIN	LGTH.	TAIL LENGTH		MATING LENGTH				BERGSTRIPTM	LF OPTION	
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	PACKAGING	NOTES	AVAILABLE		
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC					
87345-YYY	1.218	30.94	0.406	10.31	0.712	18.08	POLY BAGS	-	NO	NOTE 1,13	
87348-YYY	0.930	23.62	0.100	2.54	0.730	18.54	POLY BAGS	-	NO		
87349-YYY	0.890	22.61	0.110	2.79	0.680	17.27	POLY BAGS	-	NO		
87381-YYY	0.645	16.38	0.100	2.54	0.445	11.30	POLY BAGS	-	NO		
87382-YYY	0.675	17.15	0.100	2.54	0.475	12.07	POLY BAGS	-	NO		
87503-XXYH	0.630	16.00	0.110	2.79	0.420	10.67	POLY BAGS	-	NO		
87869-YYY	0.690	17.53	0.230	5.84	0.360	9.14	POLY BAGS	-	NO		
87894-YYY	0.588	14.94	0.170	4.32	0.318	8.08	POLY BAGS	-	NO		
87900-YYY	0.940	23.88	0.120	3.05	0.720	18.29	POLY BAGS	-	NO		
87901-YYY	1.040	26.42	0.120	3.05	0.820	20.83	POLY BAGS	-	NO		
87903-YYY	0.963	24.46	0.337	8.56	0.526	13.36	POLY BAGS	-	NO		
88797-YYY	0.950	24.13	0.320	8.13	0.530	13.46	POLY BAGS	-	NO		
88812-YYY	0.415	10.54	0.085	2.16	0.230	5.84	POLY BAGS/TUBES	NOTE 8	NO		
88886-YYY	1.306	33.17	0.276	7.01	0.930	23.62	POLY BAGS	-	NO		
89446-YYY	0.930	23.62	0.120	3.05	0.710	18.03	POLY BAGS	-	NO		
89540-YYY	0.760	19.30	0.280	7.11	0.380	9.65	POLY BAGS	-	NO		
89542-YYY	1.065	27.05	0.125	3.18	0.840	21.34	POLY BAGS	-	NO		
89639-YYY	1.260	32.00	0.118	3.00	1.042	26.47	POLY BAGS	-	NO		
91828-YYY	0.450	11.43	0.120	3.05	0.230	5.84	TUBES	-	NO		
92417-YYY	0.530	13.46	0.110	2.79	0.320	8.13	POLY BAGS	-	NO		
93216-XXYH	0.573	14.55	0.155	3.94	0.318	8.08	POLY BAGS/TUBES	-	NO		
93216-632HG	0.573	14.55	0.155	3.94	0.318	8.08	GPAX	NOTE 1	NO		
93217-XXYH	0.395	10.03	0.095	2.41	0.200	5.08	POLY BAGS	-	NO		
93254-YYY	0.563	14.30	0.110	2.79	0.353	8.97	POLY BAGS	-	NO	NOTE 1,13	

mat'l. code
NOTE 2 & 3

surface
ISO 1302 ✓

tolerance
ISO 406
ISO 1101

projection
INCH/MM
scale 2:1

product family
BERGSTIK

title
BERGSTIK II HEADER D/R
.100/2.54cc STRAIGHT

dwg no
67996

sheet 7 of 8
size
A3

type
Product Customer Drawing

sheet index

revision sheet

41

PDS: Rev :DG

STATUS: Released

Printed: Nov 16, 2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[67996-110H](#)