

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Selector switch operators

Selection and ordering data

Version	Lever type	Color of lever insert	Cam Code ²⁾	Input Voltage	Order no.	Pack unit
Selector Switches with 2 switching positions						
Maintained operation	Non-Illuminated, short lever	White	A		52SA2AAB	1
	Non-Illuminated, long lever	White	A		52SB2AAB	
	Illuminated, short lever ¹⁾		A	24V	52SA7ADN	1
	with full voltage 24V, 755 type lamp					
	Illuminated, short lever ¹⁾		A	120V	52SA7AGN	1
	with 50/60 Hz transformer 6V, 755 type lamp		A	240V	52SA7AHN	
Spring return from right operation	Non-Illuminated, short lever	White	A		52SA2ACB	1
	Non-Illuminated, long lever	White	A		52SB2ACB	
Selector Switches with 3 switching positions						
Maintained operation	Non-Illuminated, short lever	White	B		52SA2BAB	1
	Non-Illuminated, long lever	White	B		52SB2BAB	
	Non-Illuminated, short lever	White	C ³⁾		52SA2CAB	
	Non-Illuminated, long lever	White	C ³⁾		52SB2CAB	
	Non-Illuminated, short lever	White	D		52SA2DAB	
	Non-Illuminated, long lever	White	D		52SB2DAB	
	Non-Illuminated, short lever	White	E		52SA2EAB	
	Non-Illuminated, long lever	White	E		52SB2EAB	
	Non-Illuminated, short lever	White	G		52SA2GAB	
	Non-Illuminated, long lever	White	G		52SB2GAB	
	Illuminated, short lever ¹⁾		B	24V	52SA7BDN	1
	with full voltage 24V, 755 type lamp		C ³⁾	24V	52SA7CDN	
	Illuminated, short lever ¹⁾		B	120V	52SA7BGN	1
	with 50/60 Hz transformer 6V, 755 type lamp		C ³⁾	120V	52SA7CGN	
			B	240V	52SA7BHN	
			C ³⁾	240V	52SA7CHN	
Spring return from right operation	Non-Illuminated, short lever	White	B		52SA2BCB	1
	Non-Illuminated, long lever	White	B		52SB2BCB	
	Non-Illuminated, short lever	White	C ³⁾		52SA2CCB	
	Non-Illuminated, long lever	White	C ³⁾		52SB2CCB	
	Non-Illuminated, short lever	White	D		52SA2DCB	
	Non-Illuminated, long lever	White	D		52SB2DCB	
	Non-Illuminated, short lever	White	E		52SA2ECB	
	Non-Illuminated, long lever	White	E		52SB2ECB	
	Non-Illuminated, short lever	White	G		52SA2GCB	
	Non-Illuminated, long lever	White	G		52SB2GCB	
Spring return from left operation	Non-Illuminated, short lever	White	B		52SA2BBB	1
	Non-Illuminated, long lever	White	B		52SB2BBB	
	Non-Illuminated, short lever	White	C ³⁾		52SA2CBB	
	Non-Illuminated, long lever	White	C ³⁾		52SB2CBB	
	Non-Illuminated, short lever	White	D		52SA2DBB	
	Non-Illuminated, long lever	White	D		52SB2DBB	
	Non-Illuminated, short lever	White	E		52SA2EBB	
	Non-Illuminated, long lever	White	E		52SB2EBB	
	Non-Illuminated, short lever	White	G		52SA2GBB	
	Non-Illuminated, long lever	White	G		52SB2GBB	
Spring return from left and right operation	Non-Illuminated, short lever	White	B		52SA2BDB	1
	Non-Illuminated, long lever	White	B		52SB2BDB	
	Non-Illuminated, short lever	White	C ³⁾		52SA2CDB	
	Non-Illuminated, long lever	White	C ³⁾		52SB2CDB	
	Non-Illuminated, short lever	White	D		52SA2DDB	
	Non-Illuminated, long lever	White	D		52SB2DDB	
	Non-Illuminated, short lever	White	E		52SA2EDB	
	Non-Illuminated, long lever	White	E		52SB2EDB	
	Non-Illuminated, short lever	White	G		52SA2GDB	
	Non-Illuminated, long lever	White	G		52SB2GDB	
Selector Switches with 4 switching positions						
Maintained operation	Non-Illuminated, short lever	White	H		52SA2HAB	1
	Non-Illuminated, long lever	White	H		52SB2HAB	

1) Illuminated selector switches are provided without lenses. Lens kit must be ordered separately on page 10/154.

2) For contact operation, see cam selection chart on page 10/151.

3) The C cam is limited to 4 contact blocks, 1 or 2 pole.

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Selector switch operators

Selection and ordering data

Version		Color of lever insert	Cam Code ²⁾	Order no.	
					nit
Selector Pushbutton Operators					
	NEMA 12/13 only	Black	P	52SA3P1	1
	Flush type cap	Black	Q	52SA3Q1	
		Black	R	52SA3R1	
		Red	P	52SA3P2	1
		Red	Q	52SA3Q2	
		Red	R	52SA3R2	
		Black	S	52SA3S1	1
		Red	S	52SA3S2	

1) For contact operation, see cam selection chart on page 10/151.