




- NOTES:
- 1) INSULATOR MATERIAL IS LCP (LIQUID CRYSTAL POLYMER), RATED U.L. 94 V-0, COLOR IS BLACK
 - 2) TERMINAL MATERIAL IS .018"/0.46mm THICK PHOSHOR BRONZE.
 - 3) TERMINAL PLATING IS .000030/(0.00076) MINIMUM GOLD IN CONTACT AREA OVER .000100/(0.00254) MINIMUM TIN ON SOLDER TAILS, OVER NICKEL UNDERPLATE OVERALL.
 - 4) ALL DIMENSIONS ARE SHOWN FOR REFERENCE ONLY.
 - 5) THIS COMPONENT CONFORMS TO PRODUCT SPECIFICATION PS-70660.
 - 6) PACKAGE PER PK-70873-0233.

NOTE FOR LEAD FREE CONVERSION:
THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS
WITHOUT THIS LABEL MAY CONTAIN
PRODUCT WITH LEAD.

PART NUMBER	ENGINEERING NO.	DESCRIPTION
051-25-1005	71989-4002	STANDARD
051-25-1012	71989-4003	TRIMMED TO LENGTH

DIMENSIONS SHOWN (METRIC) INCH		▽ = 0		= 0		REVISE ONLY ON CAD SYSTEM													
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		TITLE		.075 PITCH LFH INSERT- MOLDED TERMINAL STRIP, 24 CKT. MALE (SALES DWG.)		SHEET NO. DATE													
<table border="1"> <tr> <th></th> <th>INCH</th> <th>METRIC</th> </tr> <tr> <td>3 PLACE</td> <td>± ---</td> <td>---</td> </tr> <tr> <td>2 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>--- ±</td> <td>± ---</td> </tr> </table>			INCH	METRIC	3 PLACE	± ---	---	2 PLACE	± ---	± ---	1 PLACE	--- ±	± ---	MOLEX INCORPORATED		U.S.A.		1 OF 1 04/21/93	
	INCH	METRIC																	
3 PLACE	± ---	---																	
2 PLACE	± ---	± ---																	
1 PLACE	--- ±	± ---																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		PART NO.		DRWG. NO.		SEE CHART SDA-71989-4001													
DRWG. BY SCHMIDGALL		CHK'D. BY CAB		FILE NAME		DIV. SIZE													
APP'D. BY CAB		SCALE 4: 1		719894001		CPPI C													

D	LEADFREE ECN# UCP2004-1663 DMORGAN 04/04/08
C	ADD PK SPEC NOTE UDT2002-0205 BSMART 01/08/02
B	REVISED PER ECN U7-0164 SCHMIDGA 96/08/15
A	FINAL RELEASE PER ECN U3-0539 04/21/93 DRS