

H.K. Porter  
HKE150 Series, 1 1/2-HP Power Pack Only - Operation of One  
Workhead

[!\[\]\(666e09182d4cd268646ea700ea60dcdf\_img.jpg\) previous](#) [print](#) [close](#) [next !\[\]\(1ef1ef0bf9af6c6996401964cf280f2d\_img.jpg\)](#)

Product Details

Catalog No.	HKE1502A
UPC Code	037103238283
Weight	137 lbs.
Horsepower	1 1/2 HP
Number of Outlets	Single
Maximum Operating Pressure	7,800 psi
Voltage/Phase/Hertz	230 V 3 PH 60 Hz
Low Voltage Control	Yes
Operation Type	Medium Duty
Packaging	No Item Level Packaging/No UPC
Stock Item	Normal Stock Item

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- 1 1/2 HP TEFC motor for dependable operation, low voltage (24 VAC)
- Lightweight design, rugged construction
- 2-stage pump delivers low pressure for rapid advance of piston
- Pump shifts to high pressure under load. Large, 1.8 gallon reservoir
- Internal relief valve protects system components from overload
- Internal filter protects system from contamination of hydraulic oil
- Control option A: Push-button control handle attached to workhead W10824
- Control option B: Heavy-duty foot switch W32368
- Control option C: Hand-held, control switch W36048
- NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!