


NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.



PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs. (g)/100pcs
ACC19-A	.19 (4.8)	.17 (77)
ACC19-AT	.19 (4.8)	.17 (77)

TO APPLY ADHESIVE CORD CLIP:

1. REMOVE PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO TOP OF CORD CLIP

* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

										(DIMENSIONS IN PARENTHESES ARE METRIC)			
										CAD FILENAME/LAYERS G00239GG_DC_01			
										PANDUIT CORP. TINLEY PARK, ILLINOIS ADHESIVE CORD CLIP ACC19-A & ACC19-AT			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± N/A (.XXX) ± N/A (.XX) ± .02 (.5) ANGLES ± 5°			
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
I	7-15-99	CGSM		REPLACED ISO VIEW	GB0239GG	I				DRAWN BY CGSM	MAT'L: NYLON 6/6	SCALE FULL	
R	2-23-99	CGSM		RE-DRAWN FROM DWG SS-7173	GB0239GG	R				DATE 2-23-99		DRAWING NO. GB0239GG	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D		DWG SIZE	