




PRODUCT NUMBER
SEE TABLE



SEE SHEET 3 FOR
LOCATOR/HOLDDOWN
VARIATIONS

.014 [0.36]
AT TIPS



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE			
ltr ecn no dr date				tolerances unless otherwise specified						title			
L J10329 CRG 6/6/01				angles		.XX±.01/0.3		INCH/MM 		RIBCAGE III T/M VERT. HEADER ASS'Y			
M M05-0123 MHT 6/6/05				linear		.XXX±.005/0.13							
N M06-0225 ERE 06/12/06				0±2°		.XXXX±.0020/0.051		scale 4:1		dwg no sheet 1 of 6 size 95776 A3			
P M06-0370 MHT 9/26/06				dr M. CORNMANN 6/6/95									
R M09-0058 MHT 4/04/09				enrg D. WHITING 6/6/95									
S N10-0122 YO 5/10/10				chr D. WHITING 6/6/95									
T ELX-N-009749 YO 1/31/12				appd D. WHITING 6/6/95									
sheet revision		T	T	T	T	T	T	type Product Customer Drawing					
index sheet		1	2	3	4	5	6						




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW




SECTION Y-Y

mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE									
ltr	ecn	no	dr	date		tolerances unless otherwise specified						title							
T						angles	linear	.XX±.01/0.3 .XXX±.005/0.13 0氣2? .XXXX±.0020/0.051		INCH/MM		RIBCAGE III T/M VERT. HEADER ASS'Y							
										scale 4:1									
						dr	M. CORNMAN	6/6/95				dwg no		sheet2 of 6		size			
						enr	D. WHITING	6/6/95				95776				A3			
						chr	D. WHITING	6/6/95											
						appd	D. WHITING	6/6/95				type Product Customer Drawing							
sheet index		revision sheet																	


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS


STYLE
1





STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code -					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE												
ltr		ecn		no		dr		date		tolerances unless otherwise specified					title								
T										angles		linear		.XX±.01/0.3		INCH/MM		RIBCAGE III T/M VERT. HEADER ASS'Y					
										0.002				.XXX±.005/0.13									
										0.002				.XXXX±.0020/0.051		scale 4:1							
										dr		M. CORNMAN		6/6/95				dwg no		sheet3 of 6		size	
										engr		D. WHITING		6/6/95				95776		A3			
										chr		D. WHITING		6/6/95				type Product Customer Drawing					
										appd		D. WHITING		6/6/95									
sheet index		revision sheet																					


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE									
ltr	ecn	no	dr	date	tolerances unless otherwise specified				INCH/MM 		title RIBCAGE III T/M VERT. HEADER ASS'Y								
T					angles	linear	.XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051												
					0氣2?				scale 4:1		dwg no 95776 sheet4 of 6 A3								
					dr	M. CORNMAN	6/6/95												
					enrg	D. WHITING	6/6/95												
					chr	D. WHITING	6/6/95												
					appd	D. WHITING	6/6/95												
sheet index		revision		sheet															


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
							dwg no		
					dr	M. CORNMANN	6/6/95	sheet 5 of 6	size
					enr	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type	
					appd	D. WHITING	6/6/95	Product Customer Drawing	
sheet	revision								
index	sheet								

