

You are here: Products » Connectors f.con » PCB connectors » Male headers » SLY 9 SMD ... » **SLY 9 SMD 040**




- ▶ Heatsinks f.cool
- ▶ Cases f.case
- ▼ **Connectors f.con**
  - ▶ Sockets
  - ▼ PCB connectors
    - **Male headers**
    - Female headers
    - Direct female connector
    - Jumpers
  - ▶ IDC-connectors
  - ▶ D-Sub connectors
  - Brackets for PC
  - ▶ Optoelectronics

## Male headers

### SLY 9 SMD 040 5 S

square 0.5 mm

add to request 



Features **Technical Drawing**

<b>Kontaktmaterial</b>	CuSn-Legierung
<b>Oberfläche Kontakt / Kontakthülse</b>	Ni+0,2µm Au Ni+4...6µm Sn
<b>surface of contact</b>	selective gold-plated
<b>no. of contacts</b>	5
<b>volume resistance</b>	≤5 mΩ
<b>Nennstrom</b>	3 A
<b>nominal voltage</b>	100 V DC
<b>test voltage</b>	500 V
<b>Material Isolierkörper</b>	PA 4,6, GF
<b>temperature range</b>	-40 °C ... +163 °C (260 °C / 10 s)
<b>class of flammibility</b>	UL 94 V-0
<b>insulation resistance</b>	>10 <sup>12</sup> Ω
<b>connection type</b>	SMD
<b>version</b>	male header
<b>reflow solderable</b>	yes
<b>packing</b>	pick and place pad and bar magazine