

Data Sheet: TL01486, TL01482, TL08620, TL02031, TL08621



HT-336FM
8.7"(220mm)

	Part Number	Die P/N	Specifications	Crimping cable size
	TL01482	3A	.256"/.068"/.213" 6.50/1.73/5.41mm	RG58, 59, 62
	TL01486	2C2	AWG 20-18/16-14 DIN 0.5-1/1.5-2.5mm ²	Non-insulated terminal or open barrel terminal
	TL08620		AWG 22-18/16-14/12-10 DIN 0.5-1.0/1.5-2.5/4-6 mm ² HT-301 DIE is unchangeable	Insulated terminal
	TL02031	3 G	.043"/.068"/.100"/.137"/.213"/.255" 1.09/1.73/2.54/3.48/5.41/6.48mm	RG58, 59, 62, 174 Fiber Optic
	TL08621	3 C	.256"/.319"/.068"/.213" 6.50/8.10/1.73/5.41mm	RG58