






REV.	DATE	DESCRIPTION
A	03/31/05	CHANGE TO .60 [.024] CENTER CONTACT



RECOMMENDED
CABLE STRIPPING DIM'S



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .178"
2. CRIMPED CONTACT PIN,
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex PART DESCRIPTION BNC CRIMP JACK (.60 [.024] I.D CONTACT) PART NO. 112161-10 DWG. NO. 112161-10.DWG REV. A SIZE A SCALE NA				
8						DRAWN	G.R.S.					03/31/05
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED						
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	ISSUED						
5	FERRULE	BRASS	NICKEL	1		SHEET	1 OF 1					
4	SLEEVE	DELFIN	NATURAL	1		CAD FILE		C:/112/112161-10.DWG				
3	CONTACT PIN	PHOS. BRONZE	GOLD	1		DO NOT SCALE DRAWING						
2	INSULATOR	DELFIN	NATURAL	1								
1	BODY	BRASS	NICKEL	1								
	DESCRIPTION	MATERIAL	FINISH	QTY								