




A




B




C

PC card drilling dimensions(after plating)  
(thickness 2.40±0.20mm)



D



## TIN LEAD PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER  |
|-------|--------|--------|--------|--------|--------|--------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.79  | 10.96  | D09P24B.G100 |
| 15    | 39.14  | 33.32  | 25.18  | 25.12  | 19.18  | D15P24B.G100 |
| 25    | 53.03  | 47.04  | 39.12  | 38.84  | 33.12  | D25P24B.G100 |
| 37    | 69.32  | 63.50  | 55.68  | 55.30  | 49.68  | D37P24B.G100 |

Protection: 4 --&gt; flash AU

6 --&gt; 0.76μ AU

## LEAD FREE PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER    |
|-------|--------|--------|--------|--------|--------|----------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.79  | 10.96  | D09P24B.G100LF |
| 15    | 39.14  | 33.32  | 25.18  | 25.12  | 19.18  | D15P24B.G100LF |
| 25    | 53.03  | 47.04  | 39.12  | 38.84  | 33.12  | D25P24B.G100LF |
| 37    | 69.32  | 63.50  | 55.68  | 55.30  | 49.68  | D37P24B.G100LF |

Protection: 4 --&gt; flash AU

6 --&gt; 0.76μ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
SEE DRAWING C01-8646-0002

European Views

|                    |        |                                       |   |                                   |                  |                       |            |
|--------------------|--------|---------------------------------------|---|-----------------------------------|------------------|-----------------------|------------|
| www.fciconnect.com |        | surface<br>ISO 1302                   | ✓ | tolerance std<br>ISO 406 ISO 1101 | projection<br>mm | size<br>A3            | Scale<br>2 |
|                    |        | TOLERANCES UNLESS OTHERWISE SPECIFIED |   | ANGULAR                           | size<br>A3       | ECN L506-0097         |            |
| Dr                 | MASSON | 2000/08/01                            |   | LINEAR                            | 0.X ± 0.1        |                       |            |
| Eng                | PESSON | 2000/08/01                            |   |                                   | 0.XX ± 0.1       |                       |            |
| Chr                | LEGARE | 2000/08/01                            |   |                                   | 0.XXX ± 0.1      |                       |            |
| Appr               | LEGARE | 2000/08/01                            |   | Product family                    | D-SUB            | Spec ref -            |            |
| FCI                |        | MALE CONNECTOR DELTA D ST             |   |                                   |                  | Rev.<br>D             |            |
|                    |        | straight,solder type for              |   |                                   |                  | C01-8646-0722         |            |
|                    |        | catalog no                            |   |                                   |                  | CUSTOMER sheet 1 of 1 |            |

| rev | ecn no    | dr  | date       |
|-----|-----------|-----|------------|
| A   | -         | MAS | 2000/08/01 |
| B   | L505-001  | MPE | 2005/03/14 |
| C   | L505-0056 | MPE | 2005/06/30 |
| D   | L506-0097 | LGO | 2006/07/28 |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |