




23 GRAMS	9.91±0.13 [.390 ±0.005]	3/8	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00457[.000150] MIN THK INSERT & FUNNEL: BRASS PER ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	55832-2
24 GRAMS	6.73±0.08 [.265 ±0.003]	1/4		55832-1
WEIGHT	"A"	"B"	MATERIAL AND FINISH	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 6/15/92 CHK WJ VOCKROTH 6/16/92 APVD AJ KAUFMAN 6/16/92 PRODUCT SPEC 108-11011 APPLICATION SPEC 114-2134 WEIGHT SEE TABLE CUSTOMER DRAWING	TE Connectivity WIRE TERMINAL, COPALUM SEALED, RING TONGUE, WIRE SIZE: 6 AL, 4 COPPER
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH SEE TABLE	NAME	
MATERIAL SEE TABLE	SEE TABLE	SCALE 4:1	SIZE A2 CAGE CODE 00779 DRAWING NO C=55832	RESTRICTED TO -