



Wiha Quality Tools
Germany

Go To
Image Index

Go To
Numerical Index

18

Toll Free: (800) 494-6104

Wiha **TORX**® SoftFinish® Screwdrivers - Ergonomic Cushion Grip Handle




362 TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
362 64	T5	60	2.4	2.5	.098	164	6.5	.05	10
362 66	T6	60	2.4	3.5	.139	164	6.5	.06	10
362 68	T7	60	2.4	3.5	.139	164	6.5	.06	10
362 70	T8	60	2.4	3.5	.139	164	6.5	.06	10
362 72	T9	60	2.4	4.0	.157	171	6.7	.10	10
362 74	T10	80	3.1	4.0	.157	191	7.5	.11	10
362 76	T15	80	3.1	4.0	.157	191	7.5	.11	10
362 78	T20	100	3.9	4.0	.157	211	8.3	.11	10
362 80	T25	100	3.9	4.5	.177	211	8.3	.12	10
362 82	T27	115	4.5	5.5	.216	233	9.2	.19	10
362 84	T30	115	4.5	6.0	.236	233	9.2	.20	10
362 86	T40	130	5.1	7.0	.275	254	10.0	.27	10
362 88	T45	130	5.1	8.0	.315	254	10.0	.31	10



362 94 Set 8 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.							
		Size	mm		Size	mm	lbs.
362 94	362 66	T6	60	362 78	T20	100	1.24
	362 70	T8	60	362 80	T25	100	
	362 74	T10	80	362 82	T27	115	
	362 76	T15	80	362 84	T30	115	



362 67 Set 12 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

									
Item No.		Size	mm	Size		mm	lbs.		
362 67	362 64	T5	60	362 76	T15	80	2.03		
	362 66	T6	60	362 78	T20	100			
	362 68	T7	60	362 80	T25	100			
	362 70	T8	60	362 82	T27	115			
	362 72	T9	60	362 84	T30	115			
	362 74	T10	80	362 86	T40	130			



362 91 Set 6 Pcs. TORX®

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item		 		 			
No.		Size	mm	Size	mm	lbs.	
362 91	362 66	T6	60	362 72	T9	60	.77
	362 68	T7	60	362 74	T10	80	
	362 70	T8	60	362 76	T15	80	

362 01 Set 6 Pcs. TORX®

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item		 		 			
No.		Size	mm	Size	mm	lbs.	
362 01	362 66	T6	60	362 76	T15	80	.83
	362 70	T8	60	362 78	T20	100	
	362 74	T10	80	362 80	T25	100	

PREVIOUS

NEXT

Wiha Tamper Resistant **TORX**® Drivers



362 TR Tamper Resistant **TORX® Screwdriver With Wiha-SoftFinish® Handle.** Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
362 69	T7s	60	2.4	3.5	.139	164	6.5	.06	10	
362 71	T8s	60	2.4	3.5	.139	164	6.5	.06	10	
362 73	T9s	60	2.4	4.0	.157	171	6.7	.10	10	
362 75	T10s	80	3.1	4.0	.157	191	7.5	.11	10	
362 77	T15s	80	3.1	4.0	.157	191	7.5	.11	10	
362 79	T20s	100	3.9	4.0	.157	211	8.3	.11	10	
362 81	T25s	100	3.9	4.5	.177	211	8.3	.11	10	
362 83	T27s	115	4.5	5.5	.216	233	9.2	.19	10	
362 85	T30s	115	4.5	6.0	.236	233	9.2	.20	10	
362 87	T40s	130	5.1	7.0	.275	254	10.0	.28	10	



362 98 Set 7 Pcs. Tamper Resistant **TORX®**

Item	No.	Size	mm	lbs.
362 98	362 69	T7s	60	.95
	362 71	T8s	60	
	362 73	T9s	60	
	362 75	T10s	80	



362 59 Set 10 Pcs. Tamper Resistant **TORX®**

Item	No.	Size	mm	lbs.
362 59	362 69	T7s	60	1.5
	362 71	T8s	60	
	362 73	T9s	60	
	362 75	T10s	80	
	362 77	T15s	80	
	362 79	T20s	100	
	362 81	T25s	100	
	362 83	T27s	115	
	362 85	T30s	115	
	362 87	T40s	130	

**See SoftFinish® Cushion Grip
Screwdrivers On Pages 65-70**

Wiha SoftFinish® ESD Safe Handle



ESD Safe (10⁶-10⁹ Ohm)

362 ESD Safe **TORX® Screwdriver, With Wiha-SoftFinish® Handle**
DIN EN 61340-5-1/ 61340-5-2 Round blade, CVM steel, hardened, hard chromed. Offers protection against electrostatic discharge. Dissipative SoftFinish® cushion grip handle, multi-component.

Item	No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
362 60	T3	60	2.4	3.5	.139	164	6.5	.06 10
362 04	T4	60	2.4	3.5	.139	164	6.5	.06 10
362 00	T5	60	2.4	3.5	.139	164	6.5	.06 10
362 06	T6	60	2.4	3.5	.139	164	6.5	.06 10
362 08	T8	60	2.4	3.5	.139	164	6.5	.06 10
362 09	T9	60	2.4	4.0	.157	171	6.7	.10 10
362 18	T10	80	3.1	4.0	.157	191	7.5	.11 10
362 19	T15	80	3.1	4.0	.157	191	7.5	.11 10
362 24	T20	100	3.9	4.0	.157	211	8.3	.11 10



362 89 Set 6 Pcs. ESD Safe **TORX® Screwdrivers**

Item	No.	Size	mm	lbs.
362 89	362 06	T6	60	.81
	362 08	T8	60	
	362 09	T9	60	
	362 18	T10	80	
	362 19	T15	80	
	362 24	T20	100	

**See ESD Safe Pliers/Cutters
& Precision Drivers On Pages 71, 127-132**