

**Industrial Ethernet
IE-PS-ST-MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



FO ST plug-in connectors according to IEC 61754-2 for
wire outer diameters 2.6 to 3 mm

General ordering data

Order No.	1968150000
Type	IE-PS-ST-MM
Version	FO connector, Plug ST, multimode, IP 20
GTIN (EAN)	4032248667147
Qty.	1 pc(s).

Industrial Ethernet IE-PS-ST-MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight	6 g
------------	-----

Temperatures

Operating temperature	-20 °C...+80 °C	Storage temperature	-40 °C...+90 °C
Installation temperature			

Downloads

GOST Approval	POCC DE.ME25.B01411.pdf
---------------	----------------------------

General data

Bending protection sleeve material	TPE	Cable pull-out force, min.	100 N
Connection 1	ST	Connection 2	Crimp
Crimp barrel material	Copper, nickel-plated	Description of article	Plug ST, multimode
Dust protection cap material	TPE	Fibre type	Multimode
Housing main material	Zinc diecast	Insertion loss	≤ 0.4 dB
Plugging cycles	1000	Protection degree	IP 20
Return loss (attenuation)	≥ 30 dB	Sheath diameter, max.	3 mm
Sheath diameter, min.	2.8 mm		

Standards

Connector standard	IEC 61754-2
--------------------	-------------

Classifications

ETIM 3.0	EC001121	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-08	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90		

Approvals

Approvals	
ROHS	Conform

**Industrial Ethernet
IE-PS-ST-MM**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing

