



1.1 Terminal boxes KL

Dimensions in mm			Model No. KL				Model No. KL			
Width	Height	Depth	Sheet steel				Stainless steel 1.4301 (AISI 304)		Stainless steel 1.4404 (AISI 316L)	
			with gland plate	Page	without gland plate	Page	without gland plate	Page	without gland plate	Page
150	150	80	—		1514.510	116	1521.010	305	1521.510 ¹⁾	305
150	150	80	—		—		1521.020 ¹⁾²⁾	305	1521.520 ¹⁾²⁾	305
150	150	120	—		1500.510	117	—		—	
200	150	80	—		1528.510	116	—		—	
200	150	120	—		1529.510	117	—		—	
200	200	80	—		1516.510	116	1523.010	305	1523.510 ¹⁾	305
200	200	80	—		—		1523.020 ¹⁾²⁾	305	1523.520 ¹⁾²⁾	305
200	200	120	—		1502.510	117	—		—	
300	150	80	—		1515.510	116	1522.010	305	1522.510 ¹⁾	305
300	150	80	—		—		1522.020 ¹⁾²⁾	305	1522.520 ¹⁾²⁾	305
300	150	120	1530.510	118	1501.510	117	—		—	
300	200	80	—		1517.510	116	1524.010	305	1524.510 ¹⁾	305
300	200	80	—		—		1524.020 ¹⁾²⁾	305	1524.520 ¹⁾²⁾	305
300	200	120	1531.510	118	1503.510	117	—		—	
300	300	120	1535.510	118	1507.510	117	1526.010	305	1526.510 ¹⁾	305
300	300	120	—		—		1526.020 ¹⁾²⁾	305	1526.520 ¹⁾²⁾	305
400	150	120	—		1589.510	117	—		—	
400	200	80	—		1518.510	116	—		—	
400	200	120	1532.510	118	1504.510	117	1525.010	305	1525.510 ¹⁾	305
400	200	120	—		—		1525.020 ¹⁾²⁾	305	1525.520 ¹⁾²⁾	305
400	300	120	1536.510	118	1508.510	117	—		—	
400	400	120	1539.510	118	1511.510	117	—		—	
500	200	120	1533.510	118	1505.510	117	—		—	
500	300	120	1537.510	118	1509.510	117	—		—	
600	200	80	—		1519.510	116	—		—	
600	200	120	1534.510	118	1506.510	117	—		—	
600	300	120	1538.510	118	1510.510	117	—		—	
600	400	120	1540.510	118	1512.510	117	—		—	
800	200	120	1542.510	118	1527.510	117	—		—	
800	400	120	1541.510	118	1513.510	117	—		—	

¹⁾ Delivery times available on request.

²⁾ With silicone seal.

Approvals (except enclosures with silicone seal):

- UL
- CSA
- TÜV

- Germanischer Lloyd
- Russian Maritime Register of Shipping
- Lloyds Register of Shipping
- Bureau Veritas
- VDE



1.1 E-Box EB

Dimensions in mm			Model No. EB	Page
Width	Height	Depth		
150	150	80	1551.500	119
150	150	120	1553.500	119
150	300	80	1545.500	119
150	300	120	1548.500	119
200	200	80	1546.500	119
200	200	120	1549.500	119
200	300	80	1552.500	119
200	300	120	1554.500	119

Dimensions in mm			Model No. EB	Page
Width	Height	Depth		
200	400	80	1547.500	119
200	400	120	1550.500	119
200	500	120	1557.500	119
300	300	120	1555.500	119
300	400	120	1556.500	119
300	400	155	1577.500	119
300	600	155	1578.500	119
300	800	155	1579.500	119

Approvals:

- UL
- CSA
- TÜV
- Germanischer Lloyd
- Norske Veritas

- Russian Maritime Register of Shipping
- Lloyds Register of Shipping
- Bureau Veritas
- VDE