



SPADE TERMINALS


File No.:   E42024  LR20812




STYLE A
Uninsulated



STYLE D
Flared Vinyl
Insulation Prefix
FVWS



STYLE E
Flared Vinyl
Insulation +
A.V. Sleeve
Prefix FVDWS




STYLE H
Funnel-Entry
Vinyl Insulation
Prefix FVXWS
Available Tape on
Reel Only -
Suffix TOR

Cable Size 0.2-0.5 sq mm				Styles Available
Dimensions				
Part No	Stud Size	B	F	
0.5-2A	2.2	4.6	4.5	A
0.3-3A	3.2	5	6	A B
0.5-3.7A	3.7	6.4	7.7	A B
0.5-4A	4.3	7	6.3	A

Cable size 0.25-1.65 sq mm				Styles Available	
Dimensions					
Part No	Stud size	B	F		
1.25-2A	2.2	4.6	4.3	A	D
1.25-B3A	3.2	5.8	6.3	A	D E
1.25-M3A	3.2	6.4	8.0	A	D
1.25-S3A	3.7	7.2	6.3	A	D E
1.25-YS3A	3.7	6.4	6.3	A	D E G H
1.25-N3A	3.7	6.2	6.3	A	D
1.25-YS4A	4.3	6.4	6.3	A	D E H
1.2 5-S4A	4.3	7.2	6.2	A	D E
1.25-4A	4.3	8.5	7.0	A	
1.25-5A	5.3	9.5	7.0	A	D

Cable size 1.04-2.63 sq mm				Styles Available	
Dimensions					
Part No	Stud size	B	F		
2-3A	3.7	8.5	7.3	A	D
2-M3A	3.2	6.0	5.0	A	D
2-YS3A	3.7	6.4	6.3	A	D E G H
2-S3A	3.7	7.2	6.5	A	D E G
2-YS4A	4.3	6.4	6.3	A	D H
2-S4A	4.3	7.2	6.5	A	D
2-5A	5.3	9.5	7.3	A	D
2-6A	6.4	12.0	11.0	A	D

Cable Size 1.04-2.63 sq mm				Styles Available	
Dimensions					
Part No	Stud size	B	F		
5.5-S3A	3.7	7.2	7.5	A	D
5.5-3A	3.7	9.5	7.5	A	D
5.5-S4A	4.3	8.5	7.5	A	D
5.5-5A	5.3	9.5	7.5	A	D
5.5-6A	6.4	13.5	12.2	A	D



REFER TO PAGES 20-21 FOR SUITABLE TOOLING